




# Catalog Number: UAT427-XMWR

## Features and Ratings




- Ring Type Meter Socket
- 200A Continuous, 250A Max., 600V AC
- Outdoor Enclosure (Type 3R)
- Painted G90 Steel
- 1 Phase, 3 Wire
- 5 Jaw Meter Socket
- Meter Socket Type UAT4
- Quad Bonded Neutral
- For Overhead or Underground Service
- RX Type Hub Opening, Cover Plate Installed



TYPE RX (SMALL) HUB OPENING COVER PLATE INSTALLED



VIEW SHOWN WITH COVER REMOVED



## Accessories

| CONDUIT HUBS (RX Type) |                     |
|------------------------|---------------------|
| TRADE SIZE             | CATALOG No.         |
| 1-1/4 INCH             | EC38597 or H38597-2 |
| 1-1/2 INCH             | EC38598 or H38598-2 |
| 2 INCH                 | EC38599 or H38599-2 |
| 2-1/2 INCH             | EC38600 or H38600-2 |
| Hub Cover Plate        | EC38595 or H38595-1 |

Meter Opening Cover Plate  
Cat No: H659-0162  
5th Jaw Kit  
Cat. No: EC659-0121

## Connectors, Wire Sizes and Torques

| CONNECTOR            | WIRE SIZE      | TORQUE       |
|----------------------|----------------|--------------|
| LINE, LOAD, NEUTRAL* | #6 - 350 kcmil | 250 IN.-LBS. |
| GROUND               | #2 - 14 AWG    | 50 IN.-LBS.  |

\* External Hex Drive 1/2"  
\* Internal Hex Drive 5/16"

© 2019 Copyright Siemens Industry, Inc.

**TALON**

**Meter Socket**

Description: **200A Cont, 5 Jaw, UAT4, 600V AC, Painted Steel Enclosure**

KAM 5/16/19 DO NOT SCALE DRAWING Dwg No: **UAT427-XMWR**