


Catalog Number: UAB417-200

Features and Ratings







- Ringless Meter Cover
- 1 Phase, 3 Wire, 240 VAC
- Painted G90 Steel
- 200A Breaker Factory Installed
- Meter Socket Rating: 200A Continuous
- 4 Jaw Meter Socket, Ringless Type Meter Cover
- 10,000 AIC Max. Rated (See Wiring Diagram for Details)
- For Overhead or Underground Service
- RX Type Hubs on Top End Wall



TYPE RX (SMALL) HUB PROVISION
COVERPLATE INSTALLED (NOT SHOWN)

Accessories

| TYPE RX HUBS | |
|-----------------|---------------------|
| Trade size (in) | Catalog number |
| 1 1/4" | EC38597 or H38597-2 |
| 1 1/2" | EC38598 or H38598-2 |
| 2" | EC38599 or H38599-2 |
| 2 1/2" | EC38600 or H38600-2 |
| Closure plate | EC38595 or H38595-1 |



| | | |
|---|-------------------------|----------------------------|
| Siemens Industry, Inc. | | |
| Meter/Breaker Combination | | |
| Description: | | |
| 200A, OH/UG, Ringless, Painted G90 Steel | | |
| NH 10/12/15 | DO NOT SCALE DRAWING | Dwg. No. UAB417-200 |