





Catalog Number: RH173CRF

Features and Ratings



- Ringless Type Meter Socket
- 200A Continuous, 200A Max., 600V AC
- Outdoor Enclosure (NEMA Type 3R)
- Painted G90 Steel Enclosure
- 1 Phase, 3 Wire
- 5 Jaw Meter Socket, 5th Jaw @ 9 o'Clock Position
- Meter Socket Type HQ-5U
- For Overhead & Underground Service
- RX Type Hub Opening, Cover Plate Installed
- Lever Bypass
- Bonded Neutral with Ground Lug
- 7/8" Barrel Lock Provision w/Bracket



Accessories

CONDUIT HUBS (RX Type)	
TRADE SIZE	CATALOG No.
1-1/4 INCH	EC38597 or H38597-2
1-1/2 INCH	EC38598 or H38598-2
2 INCH	EC38599 or H38599-2
2-1/2 INCH	EC38600 or H38600-2
Hub Cover Plate	EC38595 or H38595-1

GROUND LUG KIT Cat. No: H55303
Wire Size #4-14, Torque 50 IN-LB

GROUND LUG KIT Cat. No: H80500017
Wire Size #4-2, Torque 45 IN-LB
Wire Size #14-2/0, Torque 45 IN-LB



INSULATED NEUTRAL KIT
Cat. No: H64685-1, H64690-1

Connectors, Wire Sizes and Torques

CONNECTOR	WIRE SIZE	TORQUE
LINE, LOAD, NEUTRAL*	#6 - 350 kcmil	275 IN.-LBS.
GROUND	#14 - 2 AWG	45 IN.-LBS.

* External Hex Drive 1/2"
* Internal Hex Drive 5/16"

VIEW SHOWN WITH COVER AND SHIELD REMOVED



© 2017 Copyright Siemens Industry, Inc.

MURRAY Murray Electrical Products
Siemens Industry, Inc.

Meter Socket

Description: **200A Cont, 5 Jaw, HQ-5U, 600V AC,
Bonded Neutral w/Gnd, Painted Steel Enclosure**

KAM 4/13/17 DO NOT SCALE DRAWING Dwg No: **RH173CRF**