


# Catalog Number: UAT327-0GSP

## Features and Ratings

- Ring Type Meter Socket
- 200A Continuous, 250A Max., 600V AC
- Outdoor Enclosure (NEMA Type 3R)
- Painted G90 Steel
- 1 Phase, 3 Wire
- 4 Jaw Meter Socket
- Meter Socket Type UAT3
- For Overhead Service Only
- Small Hub Opening



TYPE RX (SMALL) HUB OPENING

### Accessories

CONDUIT HUBS (RX Type)	
TRADE SIZE	CATALOG No.
1-1/4 INCH	EC38597 or H38597-2
1-1/2 INCH	EC38598 or H38598-2
2 INCH	EC38599 or H38599-2
2-1/2 INCH	EC38600 or H38600-2

Hub Cover Plate EC38595 or H38595-1

Meter Opening Cover Plate  
Cat No: H659-0162






5th Jaw Kit  
Cat. No: EC659-0121

Sealing Ring  
Stainless Steel Snap Type: H54602  
Stainless Steel Screw Type: H9738-8001  
H9738-8002  
H9738-8003

## Connectors, Wire Sizes and Torques

CONNECTOR	WIRE SIZE	TORQUE
LINE, LOAD, NEUTRAL*	#6 - 350 kcmil	250 IN.-LBS.
GROUND	#2 - 14 AWG	50 IN.-LBS.

\* External Hex Drive 1/2"  
\* Internal Hex Drive 5/16"



© 2015 Copyright Siemens Industry, Inc.

<b>TALON</b>	
<b>Meter Socket</b>	
Description: <b>200A Cont, 4 Jaw, UAT3, 600V AC, Painted Steel Enclosure</b>	
JEL 6/30/15	DO NOT SCALE DRAWING Dwg No: <b>UAT327-0GSP</b>