

Siemens 8" LED LOR Test

LOR Reported
 LOR Not Reported

FILAMENT THRESHOLD							FLASH RATE 40				
VLO	500	700	1000	1100	1200	1300	1400	1500	1600	1700	1800
13											LOR
12.5											
12										LOR	LOR
11.5											
11								LOR	LOR	LOR	LOR
10.5											
10						LOR	LOR	LOR	LOR	LOR	LOR
9.5											
9					LOR	LOR	LOR	LOR	LOR	LOR	LOR

FILAMENT THRESHOLD							FLASH RATE 45				
VLO	500	700	1000	1100	1200	1300	1400	1500	1600	1700	1800
13											LOR
12.5											
12								LOR	LOR	LOR	LOR
11.5											
11								LOR	LOR	LOR	LOR
10.5											
10						LOR	LOR	LOR	LOR	LOR	LOR
9.5											
9					LOR	LOR	LOR	LOR	LOR	LOR	LOR

FILAMENT THRESHOLD							FLASH RATE 50				
VLO	500	700	1000	1100	1200	1300	1400	1500	1600	1700	1800
13											LOR
12.5											
12								LOR	LOR	LOR	LOR
11.5											
11								LOR	LOR	LOR	LOR
10.5											
10					LOR	LOR	LOR	LOR	LOR	LOR	LOR
9.5											
9				LOR	LOR	LOR	LOR	LOR	LOR	LOR	LOR

FILAMENT THRESHOLD							FLASH RATE 55				
VLO	500	700	1000	1100	1200	1300	1400	1500	1600	1700	1800
13											LOR
12.5											
12								LOR	LOR	LOR	LOR
11.5											
11							LOR	LOR	LOR	LOR	LOR
10.5											
10					LOR	LOR	LOR	LOR	LOR	LOR	LOR
9.5											
9				LOR	LOR	LOR	LOR	LOR	LOR	LOR	LOR

FILAMENT THRESHOLD							FLASH RATE 60				
VLO	500	700	1000	1100	1200	1300	1400	1500	1600	1700	1800
13											LOR
12.5											
12								LOR	LOR	LOR	LOR
11.5											
11							LOR	LOR	LOR	LOR	LOR
10.5											
10					LOR	LOR	LOR	LOR	LOR	LOR	LOR
9.5											
9				LOR	LOR	LOR	LOR	LOR	LOR	LOR	LOR

FILAMENT THRESHOLD							FLASH RATE 65				
VLO	500	700	1000	1100	1200	1300	1400	1500	1600	1700	1800
13									LOR	LOR	LOR
12.5											
12								LOR	LOR	LOR	LOR
11.5											
11						LOR	LOR	LOR	LOR	LOR	LOR
10.5											
10				LOR	LOR	LOR	LOR	LOR	LOR	LOR	LOR
9.5											
9			LOR	LOR	LOR	LOR	LOR	LOR	LOR	LOR	LOR

FILAMENT THRESHOLD							FLASH RATE 70				
VLO	500	700	1000	1100	1200	1300	1400	1500	1600	1700	1800
13									LOR	LOR	LOR
12.5											
12							LOR	LOR	LOR	LOR	LOR
11.5											
11						LOR	LOR	LOR	LOR	LOR	LOR
10.5											
10				LOR	LOR	LOR	LOR	LOR	LOR	LOR	LOR
9.5											
9			LOR	LOR	LOR	LOR	LOR	LOR	LOR	LOR	LOR

Siemens Mobility, Inc.
 One Penn Plaza
 11th Floor, Suite 1000, New York, NY 10119, United States
 Contact for information:
 Rail Infrastructure Headquarters, Homestead, PA 15120
 1 (800) 793-7233, siemensmobility.us@siemens.com

Printed in the USA | © 2021 Siemens Mobility, Inc. | usa.siemens.com/mobility
 Subject to changes and errors. Reference to any specific commercial products, processes, or services, or the use of any trade, firm, or corporation name is for the information and convenience of the public and does not constitute endorsement, recommendation, or favoring by their respective entities. The information given in this document only contains general descriptions and/or performance features. The requested performance features are binding only when they are expressly agreed upon in the concluded contract.