

# SIEMENS

Ingenuity for life

## TPS3 L6

True 10 Mode Protection

### Type 1 / 2 Surge Protection Device (SPD) for Service Entrance Applications – SB1, SB2, SB3, Type RCS Switchboards, Type WL Low Voltage Switchgear, Motor Control Centers and Busway Systems

#### Features:

- Mounts internal to:
  - SB1, SB2, SB3 & Type RCS switchboards
  - Type WL low voltage switchgear
  - TIASTAR motor control centers - standard 12" bucket
  - STP series busplug on SX series busway
- UL 1449-4 Type 2 SPD, UL 1283 Listed, CSA 22.2 No. 269.2
- Optional UL 1449 4th Edition Listed Type 1, CSA 22.2 No. 269.1
- Type 1 / Type 2 SPD
- Large block, individually fused, thermally protected, 50 kA MOVs
- 20 kA  $I_n$  (most models)
- 200 kA SCCR (most models)
- Rotary disconnect switch included
- All UL required OCP & safety coordination included
  - Type 1 SPDs intended for Line or Load side of Main Disconnect
  - Type 2 SPDs intended for Load side of Main Disconnect
- UL96A Lightning Protection Master Label compliant (@20kA  $I_n$ )

- Designed, manufactured and tested consistent with:
  - ANSI/IEEE C62.41.1-2002, C62.41.2-2002, C62.45-2002, C62.62-2010, C62.72-2007 & CSA C22.2 No. 269.1 and .2
  - 1992/2000 NEMA LS-1
  - NEC Article 285
  - IEC 61643, CE
- 10 year warranty


#### SPD Specifications

- Directly connected discrete protection elements between all possible modes providing true 10 mode protection
  - Surge Current Rating Per Phase
- | Per Phase | L-N    | L-G    | L-L    | N-G    |
|-----------|--------|--------|--------|--------|
| 150 kA    | 50 kA  | 50 kA  | 50 kA  | 50 kA  |
| 300 kA    | 100 kA | 100 kA | 100 kA | 100 kA |
| 450 kA    | 150 kA | 150 kA | 150 kA | 150 kA |
- 100% monitoring (Every MOV is monitored, incl. N-G)
  - EMI/RFI filtering: Active tracking up to -50 db from 10 kHz to 100 MHz (Type 2 option only, includes UL 1283 Listing)
  - Repetitive impulse: 5,000 hits
  - Less than 1/2 nanosecond response time
  - Relative humidity range: 1-95% non-condensing
  - Operating frequency: 47-63 Hz
  - Operating temperature: -25°C (-15°F) to +60°C (140°F)



- Applications
  - Provides main service entrance or downstream protection for sensitive computer and electronic loads
  - Std. redundancy use: 300kA/phase
  - Max. redundancy use: 450kA/phase
- SPD Monitoring
  - LED indicators
  - Audible alarm with silence switch and test button
  - Dry contacts
  - Surge counter
  - Rotary disconnect switch

**Ordering Information**




Example: TPS3CL645X02 = 10 mode Type 2 SPD (Default) for a 208/120V switchboard with a surge current capacity of 450 kA per phase and a surge counter

When an option is not selected, include a zero (0) in the field

**Available Accessories:  
 Ordered Separately**  
 RMSIE - Remote monitor

UL 1449 Fourth Edition - Test Data  
 Voltage Protection Rating (VPR - 6 kV, 3 kA) ❶

Voltage Code	Service Voltage	L-N	L-G	N-G	L-L	I <sub>n</sub>	SCCR	MCOV
A	120/240V, 1Ø, 3W (Fig 1)	700	700	700	1000	20 kA	100 kA	150
B	120/240V, 3Ø, 4W (Fig 3)	800 /1500	700 /1200	700	1800/1800	20 kA	200 kA	150 / 275
C	120/208V, 3Ø, 4W (Fig 2)	700	700	700	1000	20 kA	200 kA	150
E	277/480V, 3Ø, 4W (Fig 2)	1200	1200	1200	1800	20 kA	200 kA	320
K	380/220V, 3Ø, 4W (Fig 2)	1200	1200	1200	1800	20 kA	200 kA	320
S	400/230V, 3Ø, 4W (Fig 2)	1200	1200	1200	1800	20 kA	200 kA	320



**Figure 1**  
 Split  
 2 Hots, 1 Neu, 1 Grnd

**Figure 2**  
 Wye  
 3 Hots, 1 Neu, 1 Grnd

**Figure 3**  
 Hi-Leg Delta (B High)  
 3 Hots, (B High),  
 1 Neu, 1 Grnd

**Notes:**

- ❶ VPR may increase when disconnect switch is added  
 VPR may decrease for 450 kA per phase

**Siemens Industry, Inc.**  
 5400 Triangle Parkway  
 Norcross, GA 30092  
 888-333-3545  
 info.us@siemens.com

Order No. RPFL-S3L6C-0716  
 Printed in USA  
 All Rights Reserved.  
 ©2016 Siemens Industry, Inc.