

SIEMENS

Ingenuity for life

SIPROTEC 6MD85

Bay Controllers

www.siemens.com/siprotec

Description

The SIPROTEC 6MD85 bay controller is a general-purpose control and automation device with protection function. It is designed for use in all voltage levels from distribution to transmission. As part of the SIPROTEC 5 family, it enables a wealth of protection functions from the SIPROTEC library. The modular hardware permits integration of the IOs depending on the application. Adapt the hardware exactly to your requirements and rely on future-oriented solutions for protection, control, automation, monitoring, and **Power Quality – Basic**.

Main function	Bay controller for medium voltage and high to extra-high voltage switchgear with integrated operation and extensive protection functions. Powerful automation, simple configuration with DIGSI 5
Inputs and outputs	5 predefined standard variants with 4 current transformers, 4 voltage transformers, 11 to 75 binary inputs, 9 to 41 binary outputs
Hardware flexibility	Flexibly adjustable and expandable I/O quantity structure within the scope of the SIPROTEC 5 modular system. For great requirements placed on the quantity structure, the device can be extended in the second row. For example, this permits an additional 240 binary inputs (and more) to be used with the IO230 (see chapter "Hardware")
Housing width	1/3 × 19 inches to 2/1 × 19 inches

Functions

DIGSI 5 permits all functions to be configured and combined as required.

- Integrated bay controller with versatile protection function from medium to extra-high voltage
- Control of switching devices
- Synchrocheck and switchgear interlocking protection



SIPROTEC 6MD85 Bay Controller
(1/3 device with 1/6 expansion module with key switch operation panel)

- Fixed integrated electrical Ethernet RJ45 interface for DIGSI 5 and IEC 61850 (reporting and GOOSE)
- Up to 4 pluggable communication modules, usable for different and redundant protocols (IEC 61850-8-1, IEC 61850-9-2 Client, IEC 60870-5-103, IEC 60870-5-104, Modbus TCP, DNP3 serial and TCP, PROFINET IO, PROFINET IO S2 redundancy)
- Virtual network partitioning (IEEE 802.1Q - VLAN)
- Reliable data transmission via PRP and HSR redundancy protocols
- Arc protection
- Extensive cybersecurity functionality, such as role-based access control (RBAC), logging of security-related events, signed firmware, or authenticated IEEE 802.1X network access

Modular and flexible

- Simple, fast, and secure access to the device via a standard Web browser to display all information and diagnostic data, vector diagrams, single-line and device display pages
- Graphical logic editor to create powerful automation functions in the device
- Optional overcurrent protection for all voltage levels with 3-pole tripping
- Also used in switchgear with breaker-and-a-half layout
- Selective protection of overhead lines and cables with single-ended and multi-ended feeders using protection communication
- Overcurrent protection also configurable as emergency function
- Secure serial protection communication, also over great distances and all available physical media (optical fiber, twowire connections and communication networks)
- PQ - Basic: Voltage unbalance; voltage changes: over-voltage, dip, interruptions; TDD, THD, and harmonics
- Detecting operational measured variables and protection function measured values to evaluate the plant state, to support commissioning, and to analyze faults
- Synchrophasor measured values with the IEEE C37.118 protocol integrated (PMU)
- Powerful fault recording (buffer for a max. record time of 80 sec. at 8 kHz and 320 sec. at 2 kHz)
- Auxiliary functions for simple tests and commissioning
- Flexibly adjustable I/O quantity structure within the scope of the SIPROTEC 5 modular system

Benefits

- Safe and reliable automation and control of your plants
- Purposeful and simple operation of the devices and software thanks to user-friendly design
- Cybersecurity to NERC CIP and BDEW Whitepaper requirements
- Highest availability even under extreme environmental conditions by standard coating of the populated printed circuit boards

Applications

- The SIPROTEC 6MD85 bay controller is a general-purpose control and automation device with a protection function based on the SIPROTEC 5 system. The standard variants of the SIPROTEC 6MD85 device are delivered with instrument transformers. Furthermore, protection-class current transformers are also possible in SIPROTEC 6MD85 devices, thus allowing protection functions to be used. Due to its high flexibility, the device is suitable as selective protection equipment for overhead lines and cables with single-ended and multi-ended infeeds when protection communication is used. The device supports all SIPROTEC 5 system characteristics as well as detection and recording of power-quality data in the medium-voltage and subordinate low-voltage power system.



Siemens 2020
Smart Infrastructure
Digital Grid
Humboldtstrasse 59
90459 Nuremberg,
Germany

For the U.S. published by
Siemens Industry Inc.

100 Technology Drive
Alpharetta, GA 30005
United States

Customer Support: <http://www.siemens.com/csc>

© Siemens 2020. Subject to changes and errors.
SIPROTEC 6MD85_Steckbrief V1.docx_12.20

For all products using security features of OpenSSL, the following shall apply:

This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (www.openssl.org), cryptographic software written by Eric Young (eay@cryptsoft.com) and software developed by Bodo Moeller.