


UNDervOLTAGE RELEASE 24 V AC 50/60HZ ACCESSORY FOR 3VA4/5/6








| Model | |
|--------------------------------------|-------------------|
| Product brand name | SETRON |
| Product designation | Accessories |
| Design of the product | Auxiliary release |
| accessories | Auxiliary release |
| General technical data | |
| Degree of pollution | 3 |
| Overvoltage category | III |
| Apparent power consumption / maximum | 2 V·A |
| Voltage | |
| Tension assignée d'isolement Ui | 690 V |
| Surge voltage resistance | 4 kV |
| Mechanical Design | |
| Height | 65.1 mm |
| Width | 25.7 mm |
| Number of slots | 3 |
| Depth | 28.8 mm |
| Net weight | 91 g |

| | |
|---|---------|
| Tightening torque / with screw-type terminals / minimum | 0.4 N·m |
| Tightening torque / with screw-type terminals / maximum | 0.5 N·m |

| Connections according IEC | |
|--------------------------------------|----------------|
| Type of auxiliary circuit connection | AWG18 / 750 mm |
| Wire stripping length | 10 mm |

| Connections according UL | |
|--|------------|
| Wire stripping length [in] | 0.4 in |
| Tightening torque [lbf·in] / with screw-type terminals / minimum | 3.5 lbf·in |
| Tightening torque [lbf·in] / with screw-type terminals / maximum | 4.4 lbf·in |

Certificates

| General Product Approval | EMC | Declaration of Conformity | other |
|---|---|---|--|
|  CSA |  UL |  |  RCM |
|  EG-Konf. | | | Miscellaneous |

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9978-0BB20>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9978-0BB20>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9978-0BB20


CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





last modified:

11/17/2017