




SIEMENS

CATALOG NO. 3F3Y030FESCTEE SERIAL NO. SERIES H 30 kVA 60 Hz 3 PHASE 1.9 % IMP AT 135 °C		
115 °C RISE °C AVG. AMBIENT 185 °C TEMP CLASS °C MAX. AMBIENT PRIMARY (H1 H2 H3) 480V V SECONDARY(X0 X1 X2 X3) 208Y/120V V	VOLTS CONNECT 504 1 492 2 480 3 468 4 456 5 444 6 432 7	
WINDING MATERIAL CU ENCLOSURE TYPE NEMA-3R WEIGHT 555 LBS		TYPE HZQT DRY TYPE TRANSFORMER 770US E112313  
ELECTROSTATIC SHIELD		

SUITABLE FOR INDOOR OR OUTDOOR LOCATIONS BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION MANUAL
 NEMA ClassA NC Dry Type Transformer Siemens Industry, Inc. Norcross, GA

dau0001e




3F3Y030FESCTEE

REVISION	DATE	BY	DATE	BY
		DRAWN	06/06/05	JW
		CHEK'D		
		VERIF'D		

Confidential - Property of
Siemens Industry, Inc.
 Building Technologies Division

CUSTOMER	
ORDER NO.	DWG. NO. 3F3Y030FESCTEE SH 1 OF 2



All Dimensions in inches

ENCLOSURE COLOR :ANA 61 GREY – OUTDOOR

H.V.1. TERMINAL DETAIL

L.V.1. TERMINAL DETAIL

MECHANICAL TYPE LUGS INCLUDED
SUITABLE FOR #14-2 CU/AL
CONDUCTORS
1 CONDUCTOR PER PHASE

MECHANICAL TYPE LUGS INCLUDED
SUITABLE FOR #2/0-6 CU/AL
CONDUCTORS
1 CONDUCTOR PER PHASE

CUSTOMER NOTES:

- HV1 TERMINATED AT TOP REAR
- LV1 TERMINATED AT TOP FRONT

Confidential – Property of
Siemens Industry, Inc.
Building Technologies Division

REVISION	DATE	BY	DATE	BY
		DRAWN	06/06/05	JW
		CHEK'D		
		VERIF'D		

CUSTOMER	
ORDER NO.	DWG. NO. 3F3Y030FESCTEE
SH 2 OF 2	

0.0 j.wen 2010/01/21 14:02