

SIEMENS

Indoor Modular Bussed Elbow

Catalog Number

BE1, BE112

Enclosure

Type 1

Module Rating:

1200 Amps, Max.
120/240 Volts~, 1 Phase, 3 Wire
208Y/120 Volts~, 1 Phase, 3 Wire
(from 3 Phase, 4 Wire network)

For installation by Qualified Person in accordance with all local electrical codes and/or the National Electrical Code ®.

Important: Do not allow petroleum based (hydrocarbon) sprays, chemicals, solvents or any paint to contact interior components. Petroleum based chemicals can cause degradation of electrical insulating materials.

Connect Modules Using:

Quick Connect

Cat. No.

QC1

Torque

400-440 lb-in (35-36 ft.-lb.)

Short Circuit Current Rating

This device has a maximum short circuit current rating of 100,000 amps RMS symmetrical at 240 Volts ~ when used with modules listed below.

IMPORTANT - for use with:

Module

Main Breakers
Switches
Tap/Terminal Boxes
Pull Boxes
Meter Module
Meter Combinations
Extension Box
Bussed Elbow

For Use With Siemens Series#

(W)MC, WB, WEB, WXB, WBT
WMP, WMS, WS, WES
WMTB, WTB, WET, WT_PU
WMMB
(W)MM, WxMM, (W)MT, (W)ML, (W)MK, (W)MLZ(F)
WC, WCL, WCT
WMEX, WSP, WSPD
BE, WELB

Siemens Industry, Inc. Norcross, Georgia U.S.A.

DH1

40901473 0101 Rev.A

® The National Electrical Code is a registered trademark of the National Fire Protection Association.

© 2016 Copyright Siemens Industry, Inc.