

## Product Information for: TPSCCCC240RM

### Product Features and Specifications:

- \* Surge Current Rating Per Phase: 240 kA
- \* Short Circuit Current Rating: 200k per UL 1449 2nd Edition (SCCR)
- \* Surge Current Rating - L-N: 120 kA
- \* Surge Current Rating - L-G: 120 kA
- \* Surge Current Rating - N-G: 120 kA
- \* UL 1449 Suppression Voltage Rating - L-N: 330 Volts
- \* UL 1449 Suppression Voltage Rating - L-G: 330 Volts
- \* UL 1449 Suppression Voltage Rating - N-G: 330 Volts
- \* EMI/RFI Filtering: Up to -50dB from 100kHz to 100MHz dB
- \* MCOV: 150 Volts
- \* Suppression Technology: MOV
- \* Connection Method: Parallel
- \* Mounting Method: Internal to distribution equipment
- \* Installation Method: Internal
- \* Overcurrent Protection Method: Fused per mode
- \* Fuse - Available Interrupt Rating: 200,000 KAIR
- \* Thermal Cutout Circuit
- \* Replaceable Modules
- \* Modules per phase: 1 modules
- \* Module Connection Method: Bolted to backplane
- \* Dimensions: 7X10.5X4 HxWxD"
- \* Typical Weight: 10 lbs.
- \* Audible Alarm
- \* Remote Monitor
- \* Warranty Period: 5 Year

### Options:

- \* RM: Remote Monitor