



TEL (915) 590-8500  
FAX (915) 590-8510

3.75"

Enclosed Switch		Plug Fuse Type	
General Duty			
Catalog Number	Enclosure	Model	
<b>GP211N</b>	<b>Type 1</b>	<b>4</b>	
Amperes	Horsepower Rating		
<b>30</b>	Volts-PH	Std.	Max.
	120 AC-1Ø	½	2

The starting current of motors more than the standard horsepower rating may require the use of fuses with appropriate time delay characteristics. Continuous load current not to exceed 80 percent of the rating of fuses employed in other than motor circuits.

Wire Connector Information:  
 Line / Neutral Terminals: USE 14-6 Cu/ 12-6 Al 60°/75° C WIRE  
 Load Terminals: USE 14-8 Cu/ 12-8 Al 60°/75° C WIRE

WIRE SIZE:	14-10 AWG	8 AWG	6 AWG
NOMINAL TORQUE:	15 LB. IN.	18 LB. IN.	27 LB. IN.

**⚠ DANGER**  
HAZARDOUS VOLTAGE. WILL CAUSE DEATH OR SERIOUS INJURY.  
Turn off switch before removing or installing fuses. Turn off power ahead of switch before doing work inside. Close cover before turning power on.

**⚠ PELIGRO**  
VOLTAJE PELIGROSO. CAUSARÁ LA MUERTE O LESIONES GRAVES.  
Apagar el interruptor antes de remover o instalar el fusible. Desconectar el suministro de energía al interruptor antes de efectuar cualquier trabajo dentro de la unidad. Cerrar la cubierta antes de conectar la energía.

**Fuse & Short Circuit Information:**  
This switch is suitable for use on a circuit capable of delivering not more than 10,000 amperes, rms symmetrical, 240 Volts Maximum. (120 Volts Max. on single pole devices.)

**Accessories and Replacement Parts:**  
**Service Equipment:**  
To bond enclosure to neutral, use No. 10 screw provided.  
**Equipment Ground Bar Kit:** GSGK60M. USE Cu/Al 60°/75° C WIRE

WIRE SIZE:	14-10 AWG	8 AWG	6 AWG
NOMINAL TORQUE:	35 LB. IN.	40 LB. IN.	45 LB. IN.

This device has been inspected and tested.  
Inspection Record No.

**UL LISTED**  
ENCLOSED SWITCH  
Issue No. AL-265  
File No. E4776

**Murray Electrical Products**  
Siemens Industry, Inc.  
Norcross, GA 30092 U.S.A.  
Assembled in Mexico (E)

Pc. No. 410384B02

6.00"

.125" RCR

COMPANY NAME	MATERIAL	SIZE	JOB WILL NOT BE PRINTED UNLESS APPROVED BY CUSTOMER.		PART NO.
THIS DOCUMENT IS THE PROPERTY OF LABELTECH, INC. IT'S USE IS AUTHORIZED ONLY FOR RESPONDING TO A REQUEST FOR QUOTATION OR FOR THE PERFORMANCE OF WORK REQUESTED FROM LABELTECH, INC. ALL QUESTIONS MUST BE REFERRED TO THE LABELTECH, INC. PRODUCTION DEPARTMENT.	Semi-Gloss Paper	WIDTH	<input type="checkbox"/> OK TO PRINT AS IS	<input type="checkbox"/> MAKE CORRECTIONS, RESUBMIT CORRECTED PROOF	410384B02
		3.75"			<input type="checkbox"/> OK TO PRINT WITH CORRECTIONS AS MARKED
	INK COLORS		Label		
	Black		REVISION LEVEL		
			LENGTH	AUTHORIZED BY	DATE
		6.00"			DESIGNER
		CORNER RADIUS			Joel Ortega
		.125"			CHECKED BY
					DATE
					03/22/10