



DIMENSION IN INCHES

| KVA | A MAX | B MAX | C MAX | D | E | F | G | H | J | K | L MIN | M | N | WT. |
|-----|-------|-------|-------|-------|-------|-------|-------|------|------|------|-------|-------|------|-----|
| 15 | 35.13 | 22.13 | 12.38 | 33.75 | 11.81 | 19.19 | 31.06 | 1.44 | 8.00 | 8.00 | 16.88 | 13.56 | 2.63 | 385 |

| KVA | PRIMARY MAIN BREAKER | SECONDARY MAIN BREAKER | VOLTAGE | | TAPS |
|-----|----------------------|------------------------|---------|-----------|-------------|
| | | | PRIMARY | SECONDARY | |
| 15 | 40 AMP | 50 AMP | 480V | 208Y/120 | 2 x 5% BNFC |

| | NAME | DATE |
|-----------|------|---------|
| DRAWN | AJP | 5-10-16 |
| CHECKED | AJP | 5-10-16 |
| ENG APPR. | AJP | 5-10-16 |

Confidential - Property of
Siemens Industry, Inc.

| REV | C.N. | DATE |
|-----|------|---------|
| A | N/A | 5-10-16 |

UNLESS OTHERWISE SPECIFIED:
 TOLERANCES:
 IN
 X.XXX \pm .005
 X.XX \pm .02
 ANGULAR: \pm 2°
 DO NOT SCALE DRAWING

SCALE: 1:8
SHEET 1 OF 1

| TITLE: | | SIZE | DWG. NO. | REV |
|--|--|----------|-----------|----------|
| SIEMENS Sentron Power Center Three Phase 15kVA | | A | 3LPC015JA | A |