

## Product Information for: TPSA10050FR

### Product Features and Specifications:

- \* UL 1449 2nd Edition Revision (Feb 2007) Listed
- \* UL 1283 Complimentary Listing
- \* Surge Current Rating Per Phase: 50 kA
- \* Short Circuit Current Rating: 200k per UL 1449 2nd Edition (SCCR)
- \* Surge Current Rating - L-N: 25 kA
- \* Surge Current Rating - L-G: 25 kA
- \* Surge Current Rating - N-G: 19.5 kA
- \* UL 1449 Suppression Voltage Rating - L-N: 400 Volts
- \* UL 1449 Suppression Voltage Rating - L-G: 400 Volts
- \* UL 1449 Suppression Voltage Rating - N-G: 400 Volts
- \* EMI/RFI Filtering: Up to -50dB from 100kHz to 100MHz dB
- \* MCOV: 150 Volts
- \* Suppression Technology: MOV
- \* Connection Method: Parallel
- \* Disconnect Method: Circuit breaker in panel
- \* Mounting Method: Flush
- \* Installation Method: External
- \* Overcurrent Protection Method: Fused per mode
- \* Fuse - Available Interrupt Rating: 200,000 KAIR
- \* Thermal Cutout Circuit
- \* Enclosure Rating: NEMA 4X - Non Metallic
- \* Dimensions: 6X6X4 HxWxD"
- \* Typical Weight: 8 lbs.
- \* Remote Monitor
- \* Warranty Period: 5 Year

### Options:

- \* F: Flush Mount Option
- \* R: Remote Monitor Option