

## Product Information for: TPSE09100

### Product Features and Specifications:

- \* UL 1449 2nd Edition Revision (Feb 2007) Listed
- \* Surge Current Rating Per Phase: 100 kA
- \* Short Circuit Current Rating: 200k per UL 1449 2nd Edition (SCCR)
- \* Surge Current Rating - L-N: 50 kA
- \* Surge Current Rating - L-G: 50 kA
- \* UL 1449 Suppression Voltage Rating - L-N: 900 Volts
- \* UL 1449 Suppression Voltage Rating - L-G: 900 Volts
- \* MCOV: 320 Volts
- \* Suppression Technology: MOV
- \* Connection Method: Parallel
- \* Disconnect Method: Circuit breaker in panel
- \* Mounting Method: Surface
- \* Installation Method: External
- \* Overcurrent Protection Method: Fused per mode
- \* Fuse - Available Interrupt Rating: 200,000 KAIR
- \* Enclosure Rating: NEMA 4X
- \* Dimensions: 8X3X3 HxWxD"
- \* Typical Weight: 4 lbs.
- \* Warranty Period: 5 Year