




B-2

Bypass recloser assembly

Up to 38 kV, 900 A, 200 kV BIL
usa.siemens.com/mediumvoltage

Features and benefits:

- 15 kV, 25 kV, and 38 kV voltage ratings
- Factory installed on galvanized or fiberglass arm
- Adjustable pole gain provides angling option per field conditions
- Single- or double-point lift bracket
- Arm length 8' (2.4 m), 10' (3.0 m) or 12' (3.7 m) (custom phase-spacing available)
- Customer terminal pad options to simplify terminal connections
- Easy identification of bypass blades in open or closed position
- Three-pull design
- Square copper-tube blades
- High-pressure coin silver contacts
- Load-break hooks available
- Left- or right-hand bypass blade
- Custom configurations available
- Coastal environment options
- Quick installation
- Factory adjusted.




B-2 switch, single-phase, three-pull bypass

SIEMENS

Technical ratings

Series 2913	Unit	Voltage class		
Rated nominal maximum voltage	kV	15	25	38
Rated continuous current	A	600 / 900	600 / 900	600 / 900
Rated lightning impulse-withstand voltage	kV peak	110	150	200



B-2 assembly three-phase bypass



B-2 bypass assembly installed with CMR compact modular reclosers

Legal Manufacturer

Siemens Industry, Inc.
99 Bolton Sullivan Drive
Heber Springs, Arkansas 72543
United States of America

Telephone: +1 (800) 347-6659
usa.siemens.com/mediumvoltage

Order No. IC1000-F320-A234-V2-4A00
© 08.2021, Siemens Industry, Inc.

This document contains a general description of available technical options only, and its effectiveness will be subject to specific variables including field conditions and project parameters. Siemens does not make representations, warranties, or assurances as to the accuracy or completeness of the content contained herein. Siemens reserves the right to modify the technology and product specifications in its sole discretion without advance notice.