

# Terminal Blocks


## 8WA2 Terminals with Cage Clamps

### Ground terminals

#### Selection and ordering data

Dimensions <sup>1)</sup>	IEC ratings uninterrupted current IEC ratings insulation voltage	UL ratings current / voltage	Description	Color	Height H	Depth D	Order No.	Price
--------------------------	---	------------------------------------	-------------	-------	-------------	------------	-----------	-------

#### Ground terminals with 2 clamping points and connection to standard mounting rail



Terminal size 2.5 mm<sup>2</sup> · Overall width 5.2 mm AWG 28 - 14

**Ground terminal** green/yellow 60.0 28.6 **8WA2 011-1PF20**

Terminal size 4 mm<sup>2</sup> · Overall width 6.2 mm AWG 28 - 12

**Ground terminal** green/yellow 65.0 28.6 **8WA2 011-1PG20**

Terminal size 6 mm<sup>2</sup> · Overall width 8.2 mm AWG 24 - 10


**Ground terminal** green/yellow 70.0 31.0 **8WA2 011-1PH20**

Terminal size 10 mm<sup>2</sup> · Overall width 10 mm AWG 24 - 8

**Ground terminal** green/yellow 86 38 **8WA2 011-1PJ20**

Terminal size 16 mm<sup>2</sup> · Overall width 12 mm AWG 24 - 6

**Ground terminal** green/yellow 89.4 38 **8WA2 011-1PK20**




**2-contact bridge** yellow

Ground/N function:  
Links blue 10/16 mm<sup>2</sup> through-type  
terminal with 10/16 mm<sup>2</sup> PE terminal

**8WA2 854**

#### Ground terminals with 3 clamping points and connection to standard mounting rail




Terminal size 2.5 mm<sup>2</sup> · Overall width 5.2 mm AWG 28 - 14

**Ground terminal** green/yellow 73.5 28.6 **8WA2 011-1PF30**

Terminal size 4 mm<sup>2</sup> · Overall width 6.2 mm AWG 28 - 12

**Ground terminal** green/yellow 79.5 28.6 **8WA2 011-1PG30**

#### Ground terminals with 4 clamping points and connection to standard mounting rail



Terminal size 2.5 mm<sup>2</sup> · Overall width 5.2 mm AWG 24 - 14

**Ground terminal** green/yellow 87 28.6 **8WA2 011-1PF40**

1) 25.4 mm = 1 inch