

# Control Circuit Protection

## Supplementary Protection

### 3NC10 Open Cylindrical Fuse Holders

#### Features

3NC1038 open fuse holders have been certified in accordance with UL 512 and can be used with 13/32" x 1-1/2" (10 x 38 mm) fuses up to 600 V AC, 30 Amperes maximum.

- Type M Supplementary Fuse Holder for use with 13/32" x 1-1/2" (10 x 38 mm) Fuses
- Typical Supplementary Fuses: Bussmann KTK, FNQ, FNM, BAF and BAN. Includes MIDGET Class Fuses
- Ampere Rating: 32A
- Voltage Rating: 600 V
- Withstand Rating: 10,000 RMS Symmetrical (or interrupting rating of the fuse used, whichever is lower)
- Wire Range: 18 to 4 AWG
- UL Recognized, UL 512, Fuse Holder
- UL Flammability: 94VO
- Holder Material: Thermoplastic
- Surface Mounted



#### Selection and ordering

Description	Number of poles	Order Number	List Price \$	Weight Item kg
<b>Cylindrical Fuse Holder</b> Type M, Supplementary Fuses for 13/32" x 1-1/2" (10 x 38 mm)	1	<b>3NC1038-1</b>		0.042
	2	<b>3NC1038-2</b>		0.077
	3	<b>3NC1038-3</b>		0.113

#### Dimensions

