







**Catalog Number: 40007-01F**

**Features and Ratings**

- Ringless Type Meter Socket
- 200A Continuous, 200A Max., 600V AC
- Outdoor Enclosure (NEMA Type 3R)
- Painted Steel Enclosure
- 3 Phase, 4 Wire
- 7 Jaw Meter Socket
- Meter Socket Type HQ-7
- For Overhead Service Only
- RX Type Hub Opening
- Lever Bypass
- One Ground Lug Installed



VIEW SHOWN WITH COVER REMOVED



**Accessories**

| CONDUIT HUBS (RX Type) |                     |
|------------------------|---------------------|
| TRADE SIZE             | CATALOG No.         |
| 1-1/4 INCH             | EC38597 or H38597-2 |
| 1-1/2 INCH             | EC38598 or H38598-2 |
| 2 INCH                 | EC38599 or H38599-2 |
| 2-1/2 INCH             | EC38600 or H38600-2 |

Hub Cover Plate EC38595 or H38595-1

Meter Opening Cover Plate  
Cat No: H659-0162

**Connectors, Wire Sizes and Torques**

| CONNECTOR            | WIRE SIZE      | TORQUE       |
|----------------------|----------------|--------------|
| LINE, LOAD, NEUTRAL* | #6 - 350 kcmil | 275 IN.-LBS. |
| GROUND               | #14 - 2 AWG    | 45 IN.-LBS.  |

\* External Hex Drive 1/2"  
\* Internal Hex Drive 5/16"

© 2015 Copyright Siemens Industry, Inc.

|  |   |
|--|---|
| <b>TALON</b>   |   |
| <b>Meter Socket</b>  |   |
| Description: <b>200A Cont, 7 Jaw, HQ-7, 600V AC, Painted Steel Enclosure</b> |   |
| JEL 8/30/15  | DO NOT SCALE DRAWING Dwg No: <b>40007-01F</b> |