



NOT SUBJECT TO UPDATE ONCE COPIED / PRINTED OR DOWNLOADED

MATERIAL:

Dimensions in millimetres : Surface texture in micrometres. Machine where marked ✓
 For explanation of dimensions, tolerances, notes etc. see B.S.308.
 Limit on untoleranced unmachined dimensions ± _____
 Limits on untoleranced machined dimensions to B.S.4500; i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8; over 6 to 30±0.2; over 120 to 315±0.5;
 General unmachined angular tolerance ± _____

Finish: _____

Title: TYPICAL SCHEMATIC DIAGRAM 2 PHASE (DIR) + E/F (DIR) NUMERIC OVERCURRENT PROTECTION (ARGUS 2) EPSILON

First used on: _____
 Similar Articles: 2434W10023
 Supersedes: _____

Treatment: _____

Reyrolle Protection Hebburn.

Original Scale: NTS

Drg. No. 2434W10067

2	19/4/02	MN434/2292
1	22/11/99	CHANGE NOTED

Copyright © 1999 Reyrolle Ltd.

ISSUE DATE NOTED