

## Product Information for: TPSG121202FDR

### Product Features and Specifications:

- \* UL 1449 2nd Edition Revision (Feb 2007) Listed
- \* Surge Current Rating Per Phase: 120 kA
- \* Short Circuit Current Rating: 200k per UL 1449 2nd Edition (SCCR)
- \* Surge Current Rating - L-L: 40 kA
- \* Surge Current Rating - L-G: 80 kA
- \* UL 1449 Suppression Voltage Rating - L-L: 1800 Volts
- \* UL 1449 Suppression Voltage Rating - L-G: 1800 Volts
- \* EMI/RFI Filtering: Up to -50dB from 100kHz to 100MHz dB
- \* MCOV: 840 Volts
- \* Suppression Technology: MOV
- \* Connection Method: Parallel
- \* Disconnect Method: Integral disconnect switch
- \* Mounting Method: Surface
- \* Installation Method: External
- \* Overcurrent Protection Method: Fused per mode
- \* Fuse - Available Interrupt Rating: 200,000 KAIR
- \* Thermal Cutout Circuit
- \* Replaceable Modules
- \* Bus Bar Connection
- \* Enclosure Rating: NEMA 12
- \* Dimensions: 12X12X6 HxWxD"
- \* Typical Weight: 21 lbs.
- \* Audible Alarm
- \* Dry Contacts
- \* Surge Counter - Dual
- \* Remote Monitor
- \* Warranty Period: 5 Year

### Options:

- \* 2: Dual Surge Counter Option
- \* F: Flush Mount Option
- \* D: Integral Disconnect Switch
- \* R: Remote Monitor