


Catalog Number: UAT111-0GIN

Features and Ratings

- Ringless Type Meter Socket
- 135A Continuous, 135A Max., 600V AC
- Outdoor Enclosure (NEMA Type 3R)
- Painted Steel Enclosure
- 1 Phase, 3 Wire
- 4 Jaw, Ringless Type Meter Socket
- Isolated Neutral
- Meter Socket Type UAT1
- For Overhead & Underground Service
- RX Type Hub Opening



TYPE RX (SMALL) HUB OPENING

Accessories

CONDUIT HUBS (RX Type)	
TRADE SIZE	CATALOG No.
1-1/4 INCH	EC38597 or H38597-2
1-1/2 INCH	EC38598 or H38598-2
2 INCH	EC38599 or H38599-2
2-1/2 INCH	EC38600 or H38600-2

Hub Cover Plate EC38595 or H38595-1





Meter Opening Cover Plate
 Cat No: H659-0162
 5th Jaw Kit
 Cat. No: EC659-0121

Connectors, Wire Sizes and Torques

CONNECTOR	WIRE SIZE	TORQUE
LINE, LOAD*	2/0 - 14 AWG	50 IN.-LBS.
NEUTRAL	#4 - 2/0 AWG	110 IN.-LBS.
GROUND	#2 - 14 AWG	50 IN.-LBS.

* External Hex Drive 5/16"

VIEW SHOWN WITH COVER REMOVED



© 2017 Copyright Siemens Industry, Inc.

TALON
Meter Socket

Description:
**135A Cont, 4 Jaw, UAT1, 600V AC,
 Isolated Neutral, Painted Steel Enclosure**

KAM 8/30/17 DO NOT SCALE DRAWING Dwg No: **UAT111-0GIN**