

Product Information for: TPSC06240X

Product Features and Specifications:

- * UL 1449 2nd Edition Revision (Feb 2007) Listed
- * UL 1283 Complimentary Listing
- * Surge Current Rating Per Phase: 240 kA
- * Short Circuit Current Rating: 200k per UL 1449 2nd Edition (SCCR)
- * Surge Current Rating - L-N: 120 kA
- * Surge Current Rating - L-G: 120 kA
- * Surge Current Rating - N-G: 120 kA
- * UL 1449 Suppression Voltage Rating - L-N: 330 Volts
- * UL 1449 Suppression Voltage Rating - L-G: 330 Volts
- * UL 1449 Suppression Voltage Rating - N-G: 330 Volts
- * EMI/RFI Filtering: Up to -50dB from 100kHz to 100MHz dB
- * MCOV: 150 Volts
- * Suppression Technology: MOV
- * Connection Method: Parallel
- * Installation Method: Internal - Direct Bus connection
- * Overcurrent Protection Method: Fused per mode
- * Fuse - Available Interrupt Rating: 200,000 KAIR
- * Thermal Cutout Circuit
- * Module Connection Method: Bolted to bus bar
- * Dimensions: 5.26X9.20X4.32 HxWxD"
- * Audible Alarm
- * Dry Contacts
- * Surge Counter
- * Warranty Period: 5 Year

Options:

- * X: Surge Counter