

Product Information for: TPSK11080FD

Product Features and Specifications:

- * UL 1449 2nd Edition Revision (Feb 2007) Listed
- * UL 1283 Complimentary Listing
- * Surge Current Rating Per Phase: 80 kA
- * Short Circuit Current Rating: 200k per UL 1449 2nd Edition (SCCR)
- * Surge Current Rating - L-N: 40 kA
- * Surge Current Rating - L-G: 40 kA
- * Surge Current Rating - N-G: 30 kA
- * UL 1449 Suppression Voltage Rating - L-N: 800 Volts
- * UL 1449 Suppression Voltage Rating - L-G: 800 Volts
- * UL 1449 Suppression Voltage Rating - N-G: 800 Volts
- * EMI/RFI Filtering: Up to -50dB from 100kHz to 100MHz dB
- * MCOV: 320 Volts
- * Suppression Technology: MOV
- * Connection Method: Parallel
- * Disconnect Method: Circuit breaker in panel
- * Mounting Method: Flush
- * Installation Method: External
- * Overcurrent Protection Method: Fused per mode
- * Fuse - Available Interrupt Rating: 200,000 KAIR
- * Thermal Cutout Circuit
- * Enclosure Rating: NEMA 4X - Non Metallic
- * Dimensions: 6X6X4 HxWxD"
- * Typical Weight: 8 lbs.
- * Dry Contacts
- * Warranty Period: 5 Year

Options:

- * F: Flush Mount Option
- * D: Dry Contact Option