








Model	
Product brand name	SETRON
Product designation	Accessories
Design of the product	Motorized operating mechanism (MO)
accessories	Motorized operating mechanism (MO)
Mechanical Design	
Rated control supply voltage U_s with DC	24 V
Height	70 mm
Width	76.2 mm
Depth	103 mm
Net weight	578 g
Connectable conductor cross-section / solid / minimum	1.5 mm ²
Connectable conductor cross-section / solid / maximum	2.5 mm ²
Connectable conductor cross-section / finely stranded / with core end processing / minimum	1.5 mm ²
Connectable conductor cross-section / finely stranded / with core end processing / maximum	2.5 mm ²

Connections according IEC

Wire stripping length

7 mm

Certificates

General Product Approval	EMC	Declaration of Conformity	other		
 CSA	 UL	 EAC	 RCM	 EG-Konf.	Miscellaneous

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mfb=3VA9137-0HA10>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9137-0HA10>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3VA9137-0HA10

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

11/17/2017