

# Control Circuit Protection



## Supplementary Protection, AC/DC Product Range

### 5SY5 70 mm mounting depth

#### Features

- Operating voltage to EN 60898 and EN 60947-2
  - 220 V DC/pole max.
  - 440 V AC max.
- Standards: EN 60 898-1, DIN VDE 0641 Part 11, IEC 60 898
- Additional components can be retrofitted.
- **Devices do not comply with UL1077**

#### Selection and ordering data

	$I_n$	MW <sup>1)</sup>	Characteristic B		Characteristic C		Weight 1 item kg
			Order No.	List Price \$ 1 item	Order No.	List Price \$ 1 item	
<b>1-pole</b>							
	A	1	-	-	5SY5 114-7	-	0.147
	0.3		-	-	5SY5 105-7	-	
	0.5		-	-	5SY5 101-7	-	
	1		-	-	5SY5 115-7	-	
	1.6		5SY5 102-6	-	5SY5 102-7	-	
	2		-	-	5SY5 103-7	-	
	3		-	-	5SY5 104-7	-	
	4		5SY5 106-6	-	5SY5 106-7	-	
	6		-	-	5SY5 108-7	-	
	8		5SY5 110-6	-	5SY5 110-7	-	
	10		5SY5 113-6	-	5SY5 113-7	-	
	13		5SY5 116-6	-	5SY5 116-7	-	
	16		5SY5 120-6	-	5SY5 120-7	-	
	20		5SY5 125-6	-	5SY5 125-7	-	
	25		5SY5 132-6	-	5SY5 132-7	-	
	32 <sup>1)</sup>		5SY5 140-6	-	5SY5 140-7	-	
40		5SY5 150-6	-	5SY5 150-7	-		
50		5SY5 163-6	-	5SY5 163-7	-		
63							
<b>2-pole</b>							
	A	2	-	-	5SY5 214-7	-	0.304
	0.3		-	-	5SY5 205-7	-	
	0.5		-	-	5SY5 201-7	-	
	1		-	-	5SY5 215-7	-	
	1.6		-	-	5SY5 202-7	-	
	2		-	-	5SY5 203-7	-	
	3		-	-	5SY5 204-7	-	
	4		5SY5 206-6	-	5SY5 206-7	-	
	6		-	-	5SY5 208-7	-	
	8		5SY5 210-6	-	5SY5 210-7	-	
	10		5SY5 213-6	-	5SY5 213-7	-	
	13		5SY5 216-6	-	5SY5 216-7	-	
	16		5SY5 220-6	-	5SY5 220-7	-	
	20		5SY5 225-6	-	5SY5 225-7	-	
	25		5SY5 232-6	-	5SY5 232-7	-	
	32		5SY5 240-6	-	5SY5 240-7	-	
40		5SY5 250-6	-	5SY5 250-7	-		
50		5SY5 263-6	-	5SY5 263-7	-		
63							

1) MW = modular width of 18 mm.  
Depth = 70 mm.