

## Product Information for: TPSL06320

### Product Features and Specifications:

- \* UL 1449 2nd Edition Revision (Feb 2007) Listed
- \* UL 1283 Complimentary Listing
- \* Surge Current Rating Per Phase: 320 kA
- \* Short Circuit Current Rating: 200k per UL 1449 2nd Edition (SCCR)
- \* Surge Current Rating - L-N: 160 kA
- \* Surge Current Rating - L-G: 160 kA
- \* Surge Current Rating - N-G: 160 kA
- \* UL 1449 Suppression Voltage Rating - L-N: 1000 Volts
- \* UL 1449 Suppression Voltage Rating - L-G: 1000 Volts
- \* UL 1449 Suppression Voltage Rating - N-G: 1000 Volts
- \* EMI/RFI Filtering: Up to -50dB from 100kHz to 100MHz dB
- \* MCOV: 420 Volts
- \* Suppression Technology: MOV
- \* Connection Method: Parallel
- \* Disconnect Method: Integral disconnect switch
- \* Installation Method: Internal - Direct Buss connection
- \* Overcurrent Protection Method: Fused per mode
- \* Fuse - Available Interrupt Rating: 200,000 KAIR
- \* Thermal Cutout Circuit
- \* Module Connection Method: Bolted to bus bar
- \* Dimensions: 5.26X9.20X4.32 HxWxD"
- \* Audible Alarm
- \* Dry Contacts
- \* Warranty Period: 5 Year