

Product Information for: TPSCCA160SCRM

Product Features and Specifications:

- * Surge Current Rating Per Phase: 160 kA
- * Short Circuit Current Rating: 200k per UL 1449 2nd Edition (SCCR)
- * Surge Current Rating - L-N: 80 kA
- * Surge Current Rating - L-G: 80 kA
- * Surge Current Rating - N-G: 120 kA
- * UL 1449 Suppression Voltage Rating - L-N: 330 Volts
- * UL 1449 Suppression Voltage Rating - L-G: 330 Volts
- * UL 1449 Suppression Voltage Rating - N-G: 330 Volts
- * EMI/RFI Filtering: Up to -50dB from 100kHz to 100MHz dB
- * MCOV: 150 Volts
- * Suppression Technology: MOV
- * Connection Method: Parallel
- * Mounting Method: Internal to distribution equipment
- * Installation Method: Internal
- * Overcurrent Protection Method: Fused per mode
- * Fuse - Available Interrupt Rating: 200,000 KAIR
- * Thermal Cutout Circuit
- * Replaceable Modules
- * Modules per phase: 1 modules
- * Module Connection Method: Bolted to backplane
- * Dimensions: 7X10.5X4 HxWxD"
- * Typical Weight: 10 lbs.
- * Audible Alarm
- * Surge Counter
- * Remote Monitor
- * Warranty Period: 5 Year

Options:

- * SC: Surge Counter
- * RM: Remote Monitor