



3F3Y225K13BD16 - Three-Phase Ventilated-USA-DOE

PRODUCT DETAILS			
KVA:	225.00	Enclosure:	NEMA 3R Ventilated
UPC#:		Phase:	Three-Phase
Line Voltage	480V-Delta	Load Voltage	208Y/120V
E/S Shielded:	Yes	Windings:	Aluminum
Temp. rise:	80°	Hertz:	60 Hz
Taps:	2 - 2.5% FCAN; 2 - 2.5% FCBN	Approvals:	UL, cUL, DOE
		Wall Bracket:	n/a
		K-Factor:	K-13
WEIGHT AND DIMENSIONS			
Height(A):	"	Width(B):	"
Depth(C):	"	Shipping Weight:	lbs
ADDITIONAL INFORMATION			
How to Buy: Contact Siemens Distributor, Siemens Sales Rep or Configure in COMPAS Configuration Tool			

Wiring Diagram

Dimensional Drawing

T480M Wiring Diagram & Connections*

Wiring Diagram

Primary: 480
Secondary: 208Y/120

Connections		
Primary Volts	On Each Coil Jumper Taps To	Primary Lines Connect To
504	1	H1, H2, H3
492	2	H1, H2, H3
480	3	H1, H2, H3
468	4	H1, H2, H3
456	5	H1, H2, H3
Sec. Volts	Secondary Lines Connect To	
208	X1, X2, X3	
120	Between X0 and X1 or X2 or X3	
1 phase		

Figure 24

