



TIASTAR

Low-voltage **motor control centers**

Deliver the reliability and power to drive performance day and night
usa.siemens.com/mcc

By thinking beyond the standard MCC, and listening to your needs, we've raised the bar for all MCCs. Innovative features available in new combinations – like the market's first UL-witnessed arc-resistant MCC that includes high-density design – allows you to maximize your return on investment using cutting edge technology while minimizing its complexity and risks.

Arc-flash resistant

With UL-witnessed testing, tiastar sets the standard in enhanced protection for your most valuable asset. Siemens is the first manufacturer to implement arc-resistant MCCs with testing to IEEE C37.20.7-2007 and witnessed by the Underwriters Laboratory (UL). Decrease the risk of exposure to arc-flash incident energy to better protect your most valuable asset, your personnel.

Features:

- Reinforced enclosure and latching systems
- Internal venting system channels the flow of arc-fault gases
- Type 2A accessibility for protection at the front, sides, and back
- Full side sheet isolates all sections within a MCC to prevent arc faults from propagating
- Options, such as unique dual-trip setting that reduces the energy available in an arc flash and back-to-back design to save you footprint, are available.

SIEMENS

High density

The right size: fit more control into less space, while retaining easy accessibility. User-friendly engineering enables a smaller footprint. High-density design meets UL and NEMA standards while reducing size for NEMA sizes 1-4 starters and feeders, leveraging the cost advantages.

Benefits:

- Up to 10-percent weight reduction and 25-percent smaller footprint than standard design
- Modular plug-in units are easy to install and remove.

Smart

Smart MCC offerings include state-of-the-art motor control technology components and features that offer optimal motor control, protection, power monitoring, communications, and automation interfacing. Siemens tiastar Smart MCC offers the highest performance among the intelligent MCCs available today.

- **State-of-the-art technology** - Connection to process control systems using the most important communication protocols: PROFIBUS, Modbus, PROFINET, and EtherNet I/P.
- **Smart components** - SIMOCODE Pro Smart motor controller, SIRIUS 3RW44 Soft Starters, and SINAMICS G120 drives offer ideal performance and information to the user.
- **Flexibility** - As your needs grow, available expansion modules offer new functionality.
- **Troubleshooting** - User-friendly diagnostics tools enable quicker fault identification for easier troubleshooting.

Integrated drives:

- Energy savings: variable frequency drives (VFDs) enable precision adjustment of rotation speeds to achieve higher motor performance and efficiency.
- Reduced harmonics: harmonic and distortion problems (electrical noise) can have a negative effect on other components in the system. Drive options are available allowing harmonic correction to meet IEEE 519 standards.
- Increased uptime: together with Smart MCCs, VFDs allow early warnings of potential production losses. Drives are edge devices in your Industrial Internet of Things (IIoT) and digitalization strategy.

Four tiastar types:

- **Base.** Fast shipping at an economical price, yet robust and reliable with Siemens reputation.
- **High density (HD).** Anywhere physical space is at a premium, our high-density design enables greater production capacity with a smaller footprint, while conforming with UL standards and reducing capital expenses. Our ultra-efficient 6" modular units for starters sizes 1–2 deliver the performance of traditional 12" buckets at half the space.
- **18-pulse.** Designed to meet the needs of the municipal water market. Robust performance is matched by standout energy efficiency, while optional asset management features and predictive diagnostics enable quick resolution of production issues.
- **Smart.** Translate raw data into usable information to yield maximum productivity with minimum overhead. Online diagnostics and asset management increase transparency and visibility into your process, enabling instant fault protections, automated variable adjustments and proactive problem prevention.

Safety integrated components:

Provides comprehensive and integrated solutions for the manufacturing and process industry, and it protects machines and the environment, while fulfilling current and future efficiency and flexibility requirements.

Technical ratings

Item	Description
Horizontal bus ratings	600 A, 800 A, 1,200 A, 1,500 A, 2,000 A, 2,500 A ¹
Horizontal bus material	Copper with tin or silver plating
Vertical bus ratings	300 A, 600 A, 800 A
Vertical bus options	Isolated (standard), insulated and isolated (optional), or auto-shutters (optional)
Horizontal bus details	Temperature rise of 50 °C (optional) or 65 °C (standard) ² over a 40 °C ambient temperature
Bus bracing	42 kAIC, 65 kAIC, or 100 kAIC
Maximum voltage	600 V for MCC

Footnotes:

1. NEMA 1.
2. Up to 1,600 A.

Legal Manufacturer

Siemens Industry, Inc.
7000 Siemens Road
Wendell, North Carolina 27591
United States of America

Telephone: +1 (800) 347-6659
www.usa.siemens.com/mcc

Order No. EMMS-B40077-04-4AUS
© 08.2021, Siemens Industry, Inc.

This document contains a general description of available technical options only, and its effectiveness will be subject to specific variables including field conditions and project parameters. Siemens does not make representations, warranties, or assurances as to the accuracy or completeness of the content contained herein. Siemens reserves the right to modify the technology and product specifications in its sole discretion without advance notice.