



Features and Ratings

- Ringless Type Meter Socket
- 200A Max., 120/240V AC
- Outdoor Enclosure (NEMA Type 3R)
- Painted G90 Steel
- 1 Phase, 3 Wire
- 4 Jaw Meter Socket
- For Underground Service

CONNECTOR	WIRE SIZE	TORQUE
A, B, N1	#8-350kcmil	375 IN.-LBS.
N2	#6-250kcmil	275 IN.-LBS.
G1	#14-1/0 AWG	50 IN.-LBS.



© 2015 Copyright Siemens Industry, Inc.



Rainproof Combination Metering

Description:
1/SKT/BKR/PED 200A 1P DB

2/28/14 KP DO NOT SCALE DRAWING Dwg No: MP0404B1200RBC