

SIEMENS

(Supplier)
(Name)
(Address)

Name
Department
Telephone
Fax
E-Mail:

(City/State/Country)(ZIP code)

Your address
Our emblem

Date 16.08.21

TRANSPORT GUIDELINES – 08.2021 - Version 028 **Transport control of purchase deliveries – Imports from Hungary**

Ladies and Gentlemen,

The following conditions apply for goods specified in supplier conditions as „EXW / FCA”.

GENERALLY:

Please note that,

- Our order number must be noted in the transport documents.
- Transport costs billed per invoice will not be accepted.
- For Shipments classified as FCA or EXW the forwarder needs to get the ORGID of the Buyer and the SOR (“Siemens Organisation Reference” aka cost center) for his Freight invoices

For shipments containing dangerous goods you are responsible to transfer the necessary legally required dangerous goods data to the freight forwarder when placing the order. You are also responsible for packing, marking, labelling etc. in compliance with the regulation relevant to the used transport mode(s)."

CAUTION:

Shipments outlined in section 2.) can only be used if approved by the ordering Siemens department

If delivery is NOT from your country, please get instruction from us when choosing the appropriate service provider.

If this rule is not observed, the additional freight and administrative costs will be billed.

1.) Parcel deliveries / Time definite deliveries up to 70 kg (pre 09/12:00h):

In exceptions > 70 kg:

- 300 kg maximum per package
- Length x width x height in cm: 300 x 120 x 160 per package

Please use **DHL Express**

For the **initial contact DHL Express** is available as follows:

HOTLINE: +49 (0) 180 / 645 00 22
E-Mail: deSiemensAbholung@dhl.com

Time definite deliveries need to be approved by the ordering Siemens entity.

Please note the DHL account number of the paying (receiving) Siemens entity on the DHL waybill. If applicable, please ask the demand carrier for the relevant DHL account number.

Please quote at intra-community shipments (EU) the service option „ECX“. For documents from third countries please quote principally “DOX”, resp. At dutiable shipments from third countries always “WPX”.

2.) Standard Groupage deliveries up to a total weight of 1000 kg per single shipment:

Please note that standard groupage starts with 32 kg. If no bundling applies Shipments below this weight, with standard parcel measures are covered by the parcel service.

For standard shipments per truck please use:

Spedition Schenker Co. Ltd., Budapest, Hungary

For the **initial contact** call **Schenker** at:

HOTLINE: Tel.: +49 911 47722-390
Fax: +49 911 47722-8399
E-Mail: Siemens-Pickup-Road.sdag@dbschenker.com

Schenker will organize the first pickup and will then establish future contact to the nearest Schenker-branch office.

Naturally you can make special pickup arrangements with your responsible Schenker-branch office. We can provide support here if needed.

Restrictions for DB Schenker:

| Groupage standard up to: | |
|--------------------------|------------------------|
| Supplier | DB Schenker Special |
| Length | 240 cm |
| Width | 180 cm |
| Height | 220 cm |
| | |
| max. weight per package | 1200 kg |
| | |
| max. volume per package | 3 cbm per package |
| Additional | |

3.) Standard deliveries LTL / Less Truck Load > 1 ton or shipments with reloading ban:

For standard shipments per truck please use:

Spedition Schenker Co. Ltd., Budapest, Hungary

For the **initial contact** call **Spedition Schenker** at:

HOTLINE: Tel.: +49 911 47722-390

Fax: +49 911 47722-8399

E-Mail: Siemens-Pickup-Road.sdag@dbschenker.com

4.) Standard deliveries FTL / Full trailer loads

For standard shipments per truck please use:

Spedition Schenker Co. Ltd., Budapest, Hungary

For the **initial contact** call **Spedition Schenker** at:

HOTLINE: Tel.: +49 911 47722-390

Fax: +49 911 47722-8399

E-Mail: Siemens-Pickup-Road.sdag@dbschenker.com

OR

Kollmannsberger KG

For the **initial contact** call **Kollmannsberger** at:

HOTLINE: Tel.: +49(0)8456-966-123

E-Mail: mail@spedition-kollmannsberger.de

Sincerely yours