


# Catalog Number: UAB417-XPG







## Features and Ratings

- Ringless Meter Cover
- 1 Phase, 3 Wire, 240 VAC
- Painted G90 Steel
- Meter Socket Rating: 200A Continuous
- 4 Jaw Meter Socket, Ringless Type Meter Cover
- 10,000 AIC Max. Rated (See Wiring Diagram for Details)
- For Overhead or Underground Service
- RX Type Hubs on Top End Wall



### Accessories

TYPE RX HUBS	
Trade size (in)	Catalog number
1 1/4"	EC38597 or H38597-2
1 1/2"	EC38598 or H38598-2
2"	EC38599 or H38599-2
2 1/2"	EC38600 or H38600-2



<b>Siemens Industry, Inc.</b>		
<b>Meter/Breaker Combination</b>		
Description: <b>200A, OH/UG, Ringless, Painted G90 Steel</b>		
NH 10/12/15	DO NOT SCALE DRAWING	Dwg. No. <b>UAB417-XPG</b>