


# Catalog Number: 9810-9502

## Features and Ratings

- Ringless Type Meter Socket
- 480A Continuous, 600A Max., 300V AC
- Outdoor Enclosure (NEMA Type 3R)
- Painted G90 Steel Enclosure
- 1 Phase, 3-Wire
- Meter Socket Type K-4UT
- For Overhead & Underground Service
- HD Type Hub Openings, 2 Cover Plates Installed



(2) TYPE HD (LARGE) HUB OPENING COVER PLATES INSTALLED

## Accessories



CONDUIT HUBS (HD Type)	
TRADE SIZE	CATALOG No.
3 INCH	EC56856 or H56856-2
3-1/2 INCH	EC56857 or H56857-2
4 INCH	EC56858 or H56858-2
Hub Cover Plate	EC56933 or H56933S

**K4 Lexan Shield**      **K4 Manual Bypass**  
 Cat No: 5007400-K      Cat No: H56495




**Blank Sliding Cover**  
 Steel - Cat. No: HA-300529-3  
 Aluminum - Cat. No: HA-300529-4

## Connectors, Wire Sizes and Torques

CONNECTOR	PART No.	WIRE SIZE	HEX DRIVE	TORQUE
LINE	56427-M	(2) #4 - 500 kcmil	3/8"	375 IN-LBS.
LOAD	56425-M	(2) #4 - 500 kcmil	3/8"	375 IN-LBS.
NEUTRAL	56490	(2) #4 - 500 kcmil	3/8"	375 IN-LBS.
GROUND	56734	#6 - 250 kcmil	5/16"	275 IN-LBS.



VIEW SHOWN WITH COVER REMOVED



© 2016 Copyright Siemens Industry, Inc.

**TALON**

**Meter Socket**

Description: **480A Cont, 4 Terminal, K-4UT, 300V AC, Painted Steel Enclosure**

JEL 3/18/16    DO NOT SCALE DRAWING    Dwg No: **9810-9502**