




Catalog Number: 9817-9802

Features and Ratings



- Ringless Type Meter Socket
- 480A Continuous, 600A Max., 600V AC
- Outdoor Enclosure (NEMA Type 3R)
- Painted G90 Steel Enclosure
- 3 Phase, Commercial/Industrial Socket
- Meter Socket Type K-7SW
- For Overhead & Underground Service
- Two Large Hub Openings, HD Type Cover Plates Installed



(2) TYPE HD (LARGE) HUB OPENINGS
COVER PLATES INSTALLED



VIEW SHOWN WITH COVER REMOVED



Accessories

CONDUIT HUBS (HD Type)		CAT No.	DESCRIPTION
TRADE SIZE	CATALOG No.		
3 INCH	EC56856 or H56856-2	H69685-1	Bypass Isolated Neutral Kit
3-1/2 INCH	EC56857 or H56857-2	H69546-1	Hex Magnet Socket Kit
4 INCH	EC56858 or H56858-2	H69232-1	Insulated T-Handle Kit
Hub Cover Plate	EC56933 or H56933S	H65050	K-base Insulator Kit
		H63864	K-base Ground Kit

Connectors, Wire Sizes and Torques

CONNECTOR	PART No.	HEX DRIVE	WIRE SIZE	TORQUE
LINE	56732	5/16"	(2)#4 - 350 kcmil	275 IN-LBS.
LOAD	56732	5/16"	(2)#4 - 350 kcmil	275 IN-LBS.
NEUTRAL	56732	5/16"	(2)#4 - 350 kcmil	275 IN-LBS.
GROUND	56734	5/16"	#6 - 250 kcmil	275 IN-LBS.

© 2015 Copyright Siemens Industry, Inc.

TALON
Meter Socket

Description: **480A Cont, 4 Terminal, K-7SW, 600V AC, Painted Steel Enclosure**

JEL 11/30/15 | DO NOT SCALE DRAWING | Dwg No: **9817-9802**