



MATERIAL:

Dimensions in millimetres : Surface texture in micrometres.
 Machine where marked ✓
 For explanation of dimensions, tolerances, notes etc. see B.S.308.
 Limit on untoleranced unmachined dimensions ± _____
 Limits on untoleranced machined dimensions to B.S.4500;
 i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;
 over 6 to 30±0.2; over 120 to 315±0.5;
 General unmachined angular tolerance ± _____

Finish:

Title:
 TYPICAL SCHEMATIC DIAGRAM FOR 3 PHASE
 NUMERIC OVERCURRENT PROTECTION (ARGUS 1) EPSILON

First used on:
 Similar Articles: 2434W10031
 Supersedes:

Treatment:

**Reyrolle Protection
 Hebburn.**

Original Scale:
 NTS

Drq. No.
 2434W10054

DRAWN M LEASK	CHECKED	APPROVED R.D.WATSON	DATE 23/07/02	IE	OPS	PCP	Purch.Spec. TQ	EAC	CE	STD	A3
---------------	---------	---------------------	---------------	----	-----	-----	----------------	-----	----	-----	----

3	RDW	28/03/06	MN993/2793
2		18/4/02	MN434/2292
1		22/11/99	CHANGE NOTED

Copyright © 1999 Reyrolle Ltd.