


Catalog Number: MC0816B1200RGA

## Features and Ratings

- Unit Rating: 200A Max., 120/240VAC
- Meter Socket Rating: 200A Continuous
- Ringless Type Meter Socket
- Outdoor Enclosure (NEMA Type 3R)
- Painted G90 Steel
- 1 Phase, 3 Wire
- 4 Jaw Meter Socket
- For Overhead or Underground Service
- RX Type Hub Opening, Cover Plate Installed
- 208Y/120 VAC, 1 Phase, 3 Wire with 5th Jaw Installed  
(Derived From 3 Phase - 4 Wire System)



## Accessories

### CONDUIT HUBS (RX Type)

TRADE SIZE	CATALOG No.
1-1/4 INCH	EC38597
1-1/2 INCH	EC38598
2 INCH	EC38599
2-1/2 INCH	EC38600

### CONDUIT HUBS (HC Type)

TRADE SIZE	CATALOG No.
2 INCH	ECHC200
2-1/2 INCH	ECHC250
3 INCH	ECHC300

## Accessories

### Filler plate

Cat No: QF3 or ECQF3

### 2/0 - #4 Lug Kit

Cat No: ECLK2

### 5TH Jaw Assembly

Cat No: EC5J2

### Mechanical Breaker Interlock

Cat No: ECSBPK08

### Meter Socket Jumper




Cat No: ECJS

### Equipment Grounding Bar

Cat No: ECGB10

## Connectors, Wire Sizes and Torques

CONNECTOR	WIRE SIZE	TORQUE
A, B, AND N	#4 AWG - 250 kcmil	250 IN.-LBS.
NEUTRAL/GROUND BAR	#14 - 10 CU/12 - 10AL AWG	20 IN.-LBS.
	#8 AWG	25 IN.-LBS.
	#6-4 AWG	35 IN.-LBS.



SKT/BKR BOTTOM VIEW

NOTES:  
1) PLACE ITEMS IN APPROX. LOCATION SHOWN

© 2015 Copyright Siemens Industry, Inc.

**SIEMENS**  
Siemens Industry, Inc.

**RAINPROOF COMBINATION METERING**

Description:

**SKT/BKR 200A 1P HCP**

RB 6/29/15 DO NOT SCALE DRAWING Dwg No: MC0816B1200RGA