

<b>SINAMICS G110</b>	Höhe	Breite	Tiefe	Tiefe mit aufgeschnapptem Bedienfeld	<b>SINAMICS V20</b>	Höhe	Breite	Tiefe, einschließlich Bedienfeld
	height	width	depth	depth with operator panel snapped on		height	width	depth; operator panel is integrated
	mm	mm	mm	mm		mm	mm	mm
6SL32110AB112BA1	150	90	116	124	6SL3210-5BB11-2BV1	142	68	107,8
6SL32110AB112BB1	150	90	116	124	6SL3210-5BB11-2BV1	142	68	107,8
6SL32110AB112UA1	150	90	116	124	6SL3210-5BB11-2UV1	142	68	107,8
6SL32110AB112UB1	150	90	116	124	6SL3210-5BB11-2UV1	142	68	107,8
6SL32110AB125BA1	150	90	116	124	6SL3210-5BB12-5BV1	142	68	107,8
6SL32110AB125BB1	150	90	116	124	6SL3210-5BB12-5BV1	142	68	107,8
6SL32110AB125UA1	150	90	116	124	6SL3210-5BB12-5UV1	142	68	107,8
6SL32110AB125UB1	150	90	116	124	6SL3210-5BB12-5UV1	142	68	107,8
6SL32110AB137BA1	150	90	116	124	6SL3210-5BB13-7BV1	142	68	107,8
6SL32110AB137BB1	150	90	116	124	6SL3210-5BB13-7BV1	142	68	107,8
6SL32110AB137UA1	150	90	116	124	6SL3210-5BB13-7UV1	142	68	107,8
6SL32110AB137UB1	150	90	116	124	6SL3210-5BB13-7UV1	142	68	107,8
6SL32110AB155BA1	150	90	131	139	6SL3210-5BB15-5BV1	142	68	127,8
6SL32110AB155BB1	150	90	131	139	6SL3210-5BB15-5BV1	142	68	127,8
6SL32110AB155UA1	150	90	131	139	6SL3210-5BB15-5UV1	142	68	127,8
6SL32110AB155UB1	150	90	131	139	6SL3210-5BB15-5UV1	142	68	127,8
6SL32110AB175BA1	150	90	131	139	6SL3210-5BB17-5BV1	142	68	127,8
6SL32110AB175BB1	150	90	131	139	6SL3210-5BB17-5BV1	142	68	127,8
6SL32110AB175UA1	150	90	131	139	6SL3210-5BB17-5UV1	142	68	127,8
6SL32110AB175UB1	150	90	131	139	6SL3210-5BB17-5UV1	142	68	127,8
6SL32110AB211AA1	160	140	142	150	6SL3210-5BB21-1BV1	160	90	147
6SL32110AB211AB1	160	140	142	150	6SL3210-5BB21-1BV1	160	90	147
6SL32110AB211UA1	160	140	142	150	6SL3210-5BB21-1UV1	160	90	147
6SL32110AB211UB1	160	140	142	150	6SL3210-5BB21-1UV1	160	90	147
6SL32110AB215AA1	160	140	142	150	6SL3210-5BB21-5BV1	160	90	147
6SL32110AB215AB1	160	140	142	150	6SL3210-5BB21-5BV1	160	90	147

6SL32110AB215UA1	160	140	142	150	6SL3210-5BB21-5UV1	160	90	147
6SL32110AB215UB1	160	140	142	150	6SL3210-5BB21-5UV1	160	90	147
6SL32110AB222AA1	181	184	152	160	6SL3210-5BB22-2BV1	176,5	136	160
6SL32110AB222AB1	181	184	152	160	6SL3210-5BB22-2BV1	176,5	136	160
6SL32110AB222UA1	181	184	152	160	6SL3210-5BB22-2UV1	176,5	136	160
6SL32110AB222UB1	181	184	152	160	6SL3210-5BB22-2UV1	176,5	136	160
6SL32110AB230AA1	181	184	152	160	6SL3210-5BB23-0BV1	176,5	136	160
6SL32110AB230AB1	181	184	152	160	6SL3210-5BB23-0BV1	176,5	136	160
6SL32110AB230UA1	181	184	152	160	6SL3210-5BB23-0UV1	176,5	136	160
6SL32110AB230UB1	181	184	152	160	6SL3210-5BB23-0UV1	176,5	136	160
6SL32110KB112BA1	150	90	101	109	6SL3210-5BB11-2BV1	142	68	107,8
6SL32110KB112BB1	150	90	101	109	6SL3210-5BB11-2BV1	142	68	107,8
6SL32110KB112UA1	150	90	101	109	6SL3210-5BB11-2UV1	142	68	107,8
6SL32110KB112UB1	150	90	101	109	6SL3210-5BB11-2UV1	142	68	107,8
6SL32110KB125BA1	150	90	101	109	6SL3210-5BB12-5BV1	142	68	107,8
6SL32110KB125BB1	150	90	101	109	6SL3210-5BB12-5BV1	142	68	107,8
6SL32110KB125UA1	150	90	101	109	6SL3210-5BB12-5UV1	142	68	107,8
6SL32110KB125UB1	150	90	101	109	6SL3210-5BB12-5UV1	142	68	107,8
6SL32110KB137BA1	150	90	101	109	6SL3210-5BB13-7BV1	142	68	107,8
6SL32110KB137BB1	150	90	101	109	6SL3210-5BB13-7BV1	142	68	107,8
6SL32110KB137UA1	150	90	101	109	6SL3210-5BB13-7UV1	142	68	107,8
6SL32110KB137UB1	150	90	101	109	6SL3210-5BB13-7UV1	142	68	107,8
6SL32110KB155BA1	150	90	101	109	6SL3210-5BB15-5BV1	142	68	127,8
6SL32110KB155BB1	150	90	101	109	6SL3210-5BB15-5BV1	142	68	127,8
6SL32110KB155UA1	150	90	101	109	6SL3210-5BB15-5UV1	142	68	127,8
6SL32110KB155UB1	150	90	101	109	6SL3210-5BB15-5UV1	142	68	127,8
6SL32110KB175BA1	150	90	101	109	6SL3210-5BB17-5BV1	142	68	127,8
6SL32110KB175BB1	150	90	101	109	6SL3210-5BB17-5BV1	142	68	127,8
6SL32110KB175UA1	150	90	101	109	6SL3210-5BB17-5UV1	142	68	127,8
6SL32110KB175UB1	150	90	101	109	6SL3210-5BB17-5UV1	142	68	127,8