

Meter/Main Breaker Combinations

JA0816B1400RLTM

FEATURES

- UL Listed only for use as service entrance equipment
- Overhead and underground feed
- Side hinged door, only one screw required to remove door
- 22K AIC rating
- FMG and AEP approved
- Landis & Gyr type HQ lever bypass meter socket rated for 320 amps continuous
- Use HD type hubs
- Field addable 5th terminal (S35815-;
- Factory installed 200A main breaker feeding 8 branch circuits and feed-thru lugs
- Field addable type MD-T(R), MD-HT(R), MP-T and MP-HT main breaker to feed sub panel



fastfax

MURRAY

Murray Electrical Products • Siemens Energy & Automation, Inc. • 3333 Old Milton Parkway, Alpharetta, GA 30005 • 1-800-964-4114
www.murrayconnect.com

©2004 Siemens Energy & Automation, Inc. All Rights Reserved.

Siemens is a registered trademark of Siemens AG. Murray is a registered trademark of Siemens Energy & Automation, Inc. Product names mentioned may be trademarks or registered trademarks of their respective companies. Specifications are subject to change without notice.

Meter/Main Breaker Combinations

JA0816B1400RLTM

