



# Catalog Number: UAB877-200

## Features and Ratings





- Ringless Type Meter Cover
- 1 Phase, 3 Wire, 120/240V AC Max.
- 200A Main Breaker Factory Installed
- 4 Jaw, 200A Continuous Meter Socket Rating
- 10,000 AIC Max. Rated (See Wiring Diagram for Details)
- Underground Service Only
- Outdoor NEMA Type 3R,  
Painted G90 Steel Enclosure

**View Shown with  
Cover Removed**




**View Shown with Covers  
and Deadfront Removed**



## Accessories

Description	Cat. No.
5th Jaw	EC5J2
Lug Kit for parallel conductors	H58022

## Schematic, Torques & Wire Sizes



Terminal	Wire Size	Torque
A, B, & N1	#6-350 kcmil	275 lb-in
N2	#4-300 kcmil	275 lb-in
N3, N4	#4-2 AWG	50 lb-in
H58022	#6-250 kcmil	275 lb-in

**MAIN BREAKER TERMINALS**  
See markings on breaker for torque requirements and conductor rating.

© 2018 Copyright Siemens Industry, Inc.

**TALON**

## Outdoor Combination Metering

Description: **200A, 4 Jaw, UG Service, Ringless, Outdoor, Painted Steel Enclosure**

KAM 8/20/18 | DO NOT SCALE DRAWING | Dwg No: **UAB877-200**