






# Pushbutton Units and Indicator Lights

## 30 mm Heavy Duty, Watertight/Oiltight, Class 52

### Special devices

#### Selection and ordering data

	Version	Ohms / color	Order no.	Weight approx.	
				lbs.	Unit
	<b>Potentiometer operator</b> 2 Watts (Type 12/3 only)	50	52MA3B01		1
		250	52MA3B04		
		500	52MA3B06		
		1 K	52MA3B08		
		2.5 K	52MA3B10		
		5 K	52MA3B12		
		10 K	52MA3B14		
		15 K	52MA3B15		
		25 K	52MA3B16		
		100 K	52MA3B20		
		500 K	52MA3B24		
		2 M	52MA3B28		
5 M	52MA3B31				
	<b>2 Button maintained operator</b> Button remains depressed when pushed		52MA2A1A2		1
			52MA2		
	<b>Wobble stick 2.5" operator</b> For use with 52BAJ (NC) contact block		52ABW2 <sup>2)</sup>		1
			52ABW3 <sup>2)</sup>		
			52ABW6 <sup>2)</sup>		
	<b>Maintained toggle operator</b>		52ABT		1
	<b>Compact pilot lights - 11/16" mounting hole<sup>1)</sup></b> Transformer type - 120V with 6V 755 type lamp	red	52MA4G2		1
		green	52MA4G3		
		less lens	52MA4GN		

1) 11/16" mounting hole required  
 2) For use with 52BAJ (NC) contact block