



Fig. 13/115 7XV75 test switch

Function overview

The following versions are available in a flush-mounting housing:

- For feeder protection without an open star point
- For feeder protection without an open star point and with additional contacts
- For feeder protection without an open star point for two CT cores or separate ground-fault CT
- For feeder protection with an open star point
- For feeder protection with an open star point and independently switchable trip and CT circuits
- For a 3-winding transformer differential protection
- For feeder protection without an open star point with 4th CT and 4th VT input (three-stage test switch)

Description

The 7XV75 test switch serves for testing protection relays including CT circuits and command contacts. With the help of the switches located on the front side, the current and voltage inputs as well as the circuits of the protection relay to be tested are interrupted and applied to the front side. Via this plug-in connector, currents and voltages can be fed by an injection test set and the different commands and indications can be tested.

Accessories/7XV75

7XV75 test switch

Technical data

Test switch

Rated operating voltage V_n	AC 400 V
Rated operating current I_n	6 A
Test current capacity	for 1 s 150 A
	for 10 s 60 A

Unit design

Metal housing	7XP20
Dimension	1/6 of 19" wide
Weight	Approx. 3.4 kg

Selection and ordering data

Description	Order No.
7XV75 test switch	7XV750□-□CA00
Without open star point for feeder protection	0
With open star point for feeder protection	1
For 3-winding transformer differential protection	2
Without open star point for two CT cores or separate ground-fault CT	3
Without open star point for feeder protection with 4 th CT and 4 th VT input (three-stage test switch)	6
Without open star point for feeder protection and with additional contacts	7
With open star point and independently switchable trip and CT circuits for feeder protection	8
Front test plugconnection	
With 16-pin Harting connector	0
With 16 banana connectors (not available for 7XV7506)	1
Connecting cable 7XV6201 for 7XV75 test switch with 2 meter cable	
with 16-pin Harting connector and 17 isolated banana connectors 4 mm with cable marks	7XV6201-5
with 16-pin Harting connector and 17 cable end sleeves with cable marks	7XV6201-6