

Each transaction relating to the buy-back programme in shares of Siemens AG with ISIN DE0007236101 by Goldman Sachs International according to Art. 5 sec. 3 MAR in conjunction with Art. 26 sec. 1, 2 and 3 MiFIR

In red colour are the fields according to Table 2 of Annex I of Del. Regulation (EU) 2017/590

	Trading date time according to field 28	Quantity according to field 30	Price according to field 33	Price Currency according to field 34	Venue according to field 36
Aggregation 30Jul19 XETA		0	0.00000	EUR	XETA
	30-07-19 08:19:54.625753 CET	470	101.34		
	30-07-19 08:19:54.625872 CET	13	101.34		
	30-07-19 08:22:44.892297 CET	300	101.24		
	30-07-19 08:22:44.892372 CET	142	101.24		
	30-07-19 08:24:10.227131 CET	225	101.2		
	30-07-19 08:24:10.227243 CET	33	101.2		
	30-07-19 08:30:18.33000 CET	273	101.44		
	30-07-19 08:36:38.508473 CET	307	101.34		
	30-07-19 08:37:28.421375 CET	244	101.22		
	30-07-19 08:39:59.835668 CET	249	101.1		
	30-07-19 08:45:00.756304 CET	323	101.16		
	30-07-19 08:51:04.930319 CET	265	101.06		
	30-07-19 08:53:28.345465 CET	358	101		
	30-07-19 08:59:15.970713 CET	343	100.92		
	30-07-19 09:02:37.830969 CET	260	100.88		
	30-07-19 09:10:33.296845 CET	166	100.92		
	30-07-19 09:10:33.296900 CET	159	100.92		
	30-07-19 09:12:11.831053 CET	428	100.92		
	30-07-19 09:12:11.860229 CET	5	100.92		
	30-07-19 09:19:45.549951 CET	291	100.82		
	30-07-19 09:24:00.892860 CET	268	100.72		
	30-07-19 09:28:24.217570 CET	210	100.7		
	30-07-19 09:28:24.226997 CET	182	100.7		
	30-07-19 09:32:13.528278 CET	240	100.64		
	30-07-19 09:41:01.526873 CET	119	100.66		
	30-07-19 09:41:01.526950 CET	180	100.66		
	30-07-19 09:41:01.527022 CET	6	100.66		
	30-07-19 09:47:02.21646 CET	144	100.7		
	30-07-19 09:47:02.21732 CET	141	100.7		
	30-07-19 09:49:32.232562 CET	236	100.72		
	30-07-19 09:50:13.730458 CET	5	100.66		
	30-07-19 09:50:13.736732 CET	351	100.66		
	30-07-19 09:59:12.575113 CET	178	100.46		
	30-07-19 09:59:12.575165 CET	51	100.46		
	30-07-19 10:04:09.921360 CET	265	100.42		
	30-07-19 10:05:04.644902 CET	257	100.36		
	30-07-19 10:09:12.800473 CET	43	100.28		
	30-07-19 10:13:27.691525 CET	235	100.24		
	30-07-19 10:15:02.657535 CET	34	100.26		
	30-07-19 10:15:02.663907 CET	186	100.26		
	30-07-19 10:15:02.663993 CET	3	100.26		
	30-07-19 10:15:02.664055 CET	134	100.26		
	30-07-19 10:23:38.248242 CET	242	100.12		
	30-07-19 10:25:48.200435 CET	390	100.16		
	30-07-19 10:32:18.181498 CET	252	100.18		
	30-07-19 10:36:06.450980 CET	331	100.14		
	30-07-19 10:41:48.69404 CET	436	100.44		
	30-07-19 10:50:54.449922 CET	243	100.36		
	30-07-19 10:52:40.809444 CET	260	100.44		
	30-07-19 10:57:36.582145 CET	272	100.32		
	30-07-19 11:02:00.315586 CET	343	100.22		
	30-07-19 11:02:00.315707 CET	12	100.22		
	30-07-19 11:06:11.496516 CET	391	100.08		
	30-07-19 11:13:30.31726 CET	151	100.12		
	30-07-19 11:15:16.695178 CET	245	100.04		
	30-07-19 11:17:36.835991 CET	141	99.94		
	30-07-19 11:21:42.757622 CET	233	100		
	30-07-19 11:26:13.524746 CET	399	100.04		
	30-07-19 11:30:48.123599 CET	287	100.06		
	30-07-19 11:39:49.402299 CET	268	99.9		
	30-07-19 11:39:49.402388 CET	6	99.9		
	30-07-19 11:46:25.419221 CET	224	99.87		
	30-07-19 11:51:46.315885 CET	124	99.99		
	30-07-19 11:51:46.316093 CET	168	99.99		
	30-07-19 11:57:28.597119 CET	116	99.93		
	30-07-19 11:57:43.655589 CET	248	99.92		
	30-07-19 12:05:15.798305 CET	298	99.77		
	30-07-19 12:09:43.417460 CET	342	99.83		
	30-07-19 12:19:21.795924 CET	260	99.74		
	30-07-19 12:25:56.251700 CET	279	99.64		
	30-07-19 12:25:56.251818 CET	60	99.64		
	30-07-19 12:29:41.158425 CET	245	99.64		
	30-07-19 12:35:48.113990 CET	172	99.39		
	30-07-19 12:35:48.114057 CET	120	99.39		
	30-07-19 12:44:09.82897 CET	285	99.43		
	30-07-19 12:54:19.735588 CET	297	99.42		
	30-07-19 12:58:14.697005 CET	87	99.48		
	30-07-19 12:58:14.697045 CET	190	99.48		
	30-07-19 13:11:52.824235 CET	252	99.49		
	30-07-19 13:14:32.949221 CET	356	99.57		
	30-07-19 13:23:01.194810 CET	360	99.65		
	30-07-19 13:31:43.910316 CET	192	99.67		
	30-07-19 13:31:43.910436 CET	225	99.67		
	30-07-19 13:37:48.912605 CET	276	99.42		
	30-07-19 13:42:15.999213 CET	251	99.4		
	30-07-19 13:46:19.339335 CET	322	99.35		
	30-07-19 13:55:07.556675 CET	399	99.43		
	30-07-19 14:00:48.337140 CET	80	99.39		
	30-07-19 14:00:48.337214 CET	165	99.39		
	30-07-19 14:05:02.526440 CET	183	99.39		
	30-07-19 14:05:02.526555 CET	46	99.39		
	30-07-19 14:07:04.815396 CET	172	99.31		
	30-07-19 14:07:04.815977 CET	94	99.31		
	30-07-19 14:11:53.792177 CET	261	99.37		
	30-07-19 14:20:38.624549 CET	226	99.43		



Each order relating to the buy-back programme above according to Art. 5 sec. 3 MAR in conjunction with Art. 25 sec. 1 and 2 MiFIR

In red colour are the fields according to Table 2 of the Annex of Del. Regulation (EU) 2017/580; alternatively you may report the

Date and Time according to field 9	Segment MIC code according to field 16	Transaction price according to field 28	Price currency according to field 29	Buy-sell indicator according to field 32
30-07-19 08:19:54.619557 CET		101.34		
30-07-19 08:19:54.619557 CET		101.34		
30-07-19 08:22:25.179900 CET		101.24		
30-07-19 08:22:25.179900 CET		101.24		
30-07-19 08:24:10.221368 CET		101.2		
30-07-19 08:24:10.221368 CET		101.2		
30-07-19 08:30:12.396844 CET		101.44		
30-07-19 08:36:22.788381 CET		101.34		
30-07-19 08:37:28.408093 CET		101.22		
30-07-19 08:39:58.907532 CET		101.1		
30-07-19 08:44:55.43675 CET		101.16		
30-07-19 08:51:01.204555 CET		101.06		
30-07-19 08:53:28.339544 CET		101		
30-07-19 08:59:13.101697 CET		100.92		
30-07-19 09:02:35.624070 CET		100.88		
30-07-19 09:10:20.968429 CET		100.92		
30-07-19 09:10:20.968429 CET		100.92		
30-07-19 09:12:11.383328 CET		100.92		
30-07-19 09:12:11.383328 CET		100.92		
30-07-19 09:19:37.371028 CET		100.82		
30-07-19 09:24:00.571671 CET		100.72		
30-07-19 09:28:20.615023 CET		100.7		
30-07-19 09:28:20.615023 CET		100.7		
30-07-19 09:31:47.879180 CET		100.64		
30-07-19 09:40:33.887232 CET		100.66		
30-07-19 09:40:33.887232 CET		100.66		
30-07-19 09:40:33.887232 CET		100.66		
30-07-19 09:46:42.252441 CET		100.7		
30-07-19 09:46:42.252441 CET		100.7		
30-07-19 09:49:30.455648 CET		100.72		
30-07-19 09:50:12.643545 CET		100.66		
30-07-19 09:50:12.643545 CET		100.66		
30-07-19 09:59:04.118757 CET		100.46		
30-07-19 09:59:04.118757 CET		100.46		
30-07-19 10:03:52.454725 CET		100.42		
30-07-19 10:04:45.623132 CET		100.36		
30-07-19 10:09:12.794530 CET		100.28		
30-07-19 10:12:59.410902 CET		100.24		
30-07-19 10:15:02.638888 CET		100.26		
30-07-19 10:15:02.638888 CET		100.26		
30-07-19 10:15:02.638888 CET		100.26		
30-07-19 10:15:02.638888 CET		100.26		
30-07-19 10:23:08.103424 CET		100.12		
30-07-19 10:25:43.700552 CET		100.16		
30-07-19 10:32:16.911282 CET		100.18		
30-07-19 10:35:51.564098 CET		100.14		
30-07-19 10:41:46.880312 CET		100.44		
30-07-19 10:50:33.210557 CET		100.36		
30-07-19 10:52:15.740263 CET		100.44		
30-07-19 10:57:17.428848 CET		100.32		
30-07-19 11:01:16.250971 CET		100.22		
30-07-19 11:01:16.250971 CET		100.22		
30-07-19 11:06:07.181524 CET		100.08		
30-07-19 11:13:11.599971 CET		100.12		
30-07-19 11:15:16.624420 CET		100.04		
30-07-19 11:17:36.830238 CET		99.94		
30-07-19 11:21:25.586360 CET		100		
30-07-19 11:25:32.172870 CET		100.04		
30-07-19 11:30:47.622945 CET		100.06		
30-07-19 11:39:29.320655 CET		99.9		
30-07-19 11:39:29.320655 CET		99.9		
30-07-19 11:46:22.96989 CET		99.87		
30-07-19 11:51:37.938120 CET		99.99		
30-07-19 11:51:37.938120 CET		99.99		
30-07-19 11:57:28.591172 CET		99.93		
30-07-19 11:57:43.649974 CET		99.92		
30-07-19 12:05:15.792334 CET		99.77		
30-07-19 12:09:41.916945 CET		99.83		
30-07-19 12:19:21.65754 CET		99.74		
30-07-19 12:25:40.289240 CET		99.64		
30-07-19 12:25:40.289240 CET		99.64		
30-07-19 12:29:36.393907 CET		99.64		
30-07-19 12:35:45.442964 CET		99.39		
30-07-19 12:35:45.442964 CET		99.39		
30-07-19 12:44:08.910983 CET		99.43		
30-07-19 12:54:17.487988 CET		99.42		
30-07-19 12:58:09.295482 CET		99.48		
30-07-19 12:58:09.295482 CET		99.48		
30-07-19 13:11:28.34894 CET		99.49		
30-07-19 13:14:32.562326 CET		99.57		
30-07-19 13:22:58.380348 CET		99.65		
30-07-19 13:31:32.947425 CET		99.67		
30-07-19 13:31:32.947425 CET		99.67		
30-07-19 13:37:19.683014 CET		99.42		
30-07-19 13:42:14.293019 CET		99.4		
30-07-19 13:45:52.926357 CET		99.35		
30-07-19 13:55:05.645576 CET		99.43		
30-07-19 14:00:44.582070 CET		99.39		
30-07-19 14:00:44.582070 CET		99.39		
30-07-19 14:05:01.905606 CET		99.39		
30-07-19 14:05:01.905606 CET		99.39		
30-07-19 14:07:03.466394 CET		99.31		
30-07-19 14:07:03.466394 CET		99.31		
30-07-19 14:11:41.74865 CET		99.37		

