

POSITION SIGNALING SWITCH FOR ACCESSORY FOR: PLUG-IN  
-OUT AND DRAW-OUT UNIT



Model	
Product brand name	SETRON
Product designation	Position signaling switch
Design of the product	Accessories plug-in/draw-out unit
accessories	Position signaling switch

General technical data	
Degree of pollution	3
Overvoltage category	III

Voltage	
Tension assignée d'isolement $U_i$	240 V
Tension assignée de tenue aux chocs	4 kV
Operating voltage / at AC / acc. to CSA and UL	240 V
Operating voltage / at DC / acc. to CSA and UL	250 V
Rated operational voltage $U_e$ at AC 50 Hz	240 V
Rated operational voltage $U_e$ with DC	250 V

Electricity	
Thermal current	6 A
Operating current	

• at AC-12 / at 12 V	6 A
• at AC-12 / at 24 V	6 A
• at AC-12 / at 48 V	6 A
• at AC-12 / at 110 V	6 A
• at AC-12 / at 230 V	6 A
• at DC-12 / at 12 V	6 A
• at DC-12 / at 24 V	3 A
• at DC-12 / at 48 V	1 A
• at DC-12 / at 110 V	0.5 A
• at DC-12 / at 230 V	0.25 A

### Mechanical Design

Height	43 mm
Width	8.5 mm
Depth	33 mm
Net weight	33 g
Tightening torque / with screw-type terminals / minimum	0.4 N·m
Tightening torque / with screw-type terminals / maximum	0.5 N·m






### Connections according IEC

Wire stripping length	15 mm
Connectable conductor cross-section	
• minimum	0.5 mm <sup>2</sup>
• maximum	1.5 mm <sup>2</sup>
AWG number / as coded connectable conductor cross section / for auxiliary contacts	
• minimum	20
• maximum	16

### Connections according UL

Wire stripping length [in]	0.6 in
Tightening torque [lbf·in] / with screw-type terminals / minimum	3.5 lbf·in
Tightening torque [lbf·in] / with screw-type terminals / maximum	4.4 lbf·in

### Certificates

General Product Approval	EMC	Declaration of Conformity	other
 CSA  UL	 EAC  RCM	 EG-Konf.	<a href="#">Miscellaneous</a>

#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9977-0KB00>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9977-0KB00>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**



[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3VA9977-0KB00](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9977-0KB00)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



**last modified:**

11/17/2017