



Standard Dimensions in Millimeters [Inches] / IEC Designations (NEMA Designations in Parentheses)														
IEC Designation	A	B	BB	C <sub>a</sub>	L <sub>2,7</sub>	E	-	G	F	D	-	SS	LE	Approx. Max Wt. kgs [lbs]
NEMA Designation	(2E)	(2F)	(B)	(BA) <sub>a</sub>	(C) <sub>2,7</sub>	(N-W)	(V) <sub>3</sub>	(R)	(S)	(U)	(ES)	(Key Height)	(Top Cover)	
SH710/712 6 Pole +	1500 [59.06]	2000 [78.74]	2510 [98.82]	355 [13.19]	4198 [165.3]	330 [12.99]	324 [12.75]	220 [8.66]	56 [2.20]	240 [9.45]	277 [10.91]	32 [1.26]	3561 [140.20]	21,200 [46,737]
SH714/716 6 Pole +	1500 [59.06]	2240 [88.19]	2750 [108.27]	355 [13.19]	4288 [168.82]	330 [12.99]	324 [12.75]	220 [8.66]	56 [2.20]	240 [9.45]	277 [10.91]	32 [1.26]	3801 [149.65]	24,000 [52,910]

**Certification:** Customer \_\_\_\_\_ P.O. \_\_\_\_\_ S.O. \_\_\_\_\_ Item \_\_\_\_\_  
 HP \_\_\_\_\_ RPM \_\_\_\_\_ Frame \_\_\_\_\_ PH/HZ/Volts 3/ \_\_\_\_\_ / \_\_\_\_\_ Terminal Box Size: 1XF5   
 Customer Tag # \_\_\_\_\_ By \_\_\_\_\_ Date \_\_\_\_\_  
 Comments \_\_\_\_\_  
 Not for construction, installation or application purposes unless certified.