

**Lista de precios de protección para base instalada DI PA AE PRO (PCS 7) FY'22**  
**Vigencia de precios de febrero 15 hasta el 30 de agosto del año 2022.**

No.	MLFB	Descripción
1	<a href="#">6ES7400-1JA01-0AA0</a>	SIMATIC S7-400, rack UR2, central and distributed with 9 slots, 2 redundant PS can be plugged in
2	<a href="#">6ES7400-1JA11-0AA0</a>	SIMATIC S7-400, rack aluminum UR2, central and distributed with 9 slots, 2 redundant PS can be plugged in
3	<a href="#">6ES7400-1JA11-0AA1</a>	SIMATIC PCS 7, UR2 XTR S7-400 rack central and distributed with 9 slots, 2 redundant PS can be plugged in for extended temperature range and with conformal coating
4	<a href="#">6ES7400-1TA01-0AA0</a>	SIMATIC S7-400, rack UR1, central and distributed with 18 slots, 2 redundant PS can be plugged in
5	<a href="#">6ES7400-1TA11-0AA0</a>	SIMATIC S7-400, rack UR1 Alu, central and distributed with 18 slots, 2 redundant PS can be plugged in
6	<a href="#">6ES7400-2JA00-0AA0</a>	SIMATIC S7-400H, rack UR2-H, central and distributed with 2 x 9 slots,
7	<a href="#">6ES7400-2JA10-0AA0</a>	SIMATIC S7-400, rack aluminum UR2-H, central and distributed with 2 x 9 slots
8	<a href="#">6ES7400-2JA10-0AA1</a>	SIMATIC PCS 7-400, UR2-H XTR S7-400 rack central and distributed with 2 x 9 slots, 2 x 2 redundant PS can be plugged in for extended temperature range and with conformal coating
9	<a href="#">6ES7401-1DA01-0AA0</a>	SIMATIC S7-400, rack CR3, central with 4 slots
10	<a href="#">6ES7401-1DA01-0AA1</a>	SIMATIC PCS 7, CR3 XTR S7-400 rack central with 4 slots for extended temperature range and with conformal coating
11	<a href="#">6ES7401-2TA01-0AA0</a>	SIMATIC S7-400, rack CR2, central, 18 slots, 2 segments 2 redundant PS can be plugged in
12	<a href="#">6ES7403-1JA01-0AA0</a>	SIMATIC S7-400, extension rack ER2 with 9 slots, only for signal modules 2 redundant PS can be plugged in
13	<a href="#">6ES7403-1JA11-0AA0</a>	SIMATIC S7-400, extended rack ER2 aluminum, with 9 slots, for signal modules, 2 redundant PS can be plugged in
14	<a href="#">6ES7403-1TA01-0AA0</a>	SIMATIC S7-400, extension rack ER1 with 18 slots, only for signal modules 2 redundant PS can be plugged in
15	<a href="#">6ES7403-1TA11-0AA0</a>	SIMATIC S7-400, ext. rack ER1 aluminum, with 18 slots, for signal modules, 2 redundant PS can be plugged in
16	<a href="#">6ES7405-0DA02-0AA0</a>	SIMATIC S7-400, power supply PS 405: 4 A, 24/48/60 V DC, 5 V DC/4 A,
17	<a href="#">6ES7405-0DA02-0AA1</a>	SIMATIC PCS 7, PS 405 4A XTR S7-400 power supply Wide range, 24/48/60 V DC; 5 V DC/4 A, ATEX approbation identifier for extended temperature range and with conformal coating
18	<a href="#">6ES7405-0KA02-0AA0</a>	SIMATIC S7-400, Power supply PS405, wide range 10 A, 24/48/60 V DC; 5 V DC/10 A ATEX approval marking
19	<a href="#">6ES7405-0KR02-0AA0</a>	SIMATIC S7-400, power supply PS405: 10 A, wide range, 24/48/60 V DC; 5 V DC/10 A, for redundant use
20	<a href="#">6ES7405-0KR02-0AA1</a>	SIMATIC PCS 7, PS 405 10A R XTR S7-400 power supply Wide range, 24/48/60 V DC; 5 V DC/10 A, for redundant use, ATEX approbation identifier for extended temperature range and with conformal coating
21	<a href="#">6ES7405-0RA02-0AA0</a>	SIMATIC S7-400, Power supply PS405: 20 A, wide range, 24/48/60 V DC, 5 V DC/20 A, ATEX approval marking
22	<a href="#">6ES7407-0DA02-0AA0</a>	SIMATIC S7-400, Power supply PS407: 4 A, wide range, UC 120/230V, 5 V DC/4 A
23	<a href="#">6ES7407-0DA02-0AA1</a>	SIMATIC PCS 7, PS 407 4A XTR S7-400 power supply Wide range, 120/230 V UC; 5 V DC/4 A, for extended temperature range and with conformal coating
24	<a href="#">6ES7407-0KA02-0AA0</a>	SIMATIC S7-400, Power supply PS407: 10 A, wide range, UC 120/230V, 5 V DC/10 A
25	<a href="#">6ES7407-0KR02-0AA0</a>	SIMATIC S7-400, Power supply PS407; 10 A, wide range, UC 120/230V, 5 V DC/10 A, for redundant use
26	<a href="#">6ES7407-0KR02-0AA1</a>	SIMATIC PCS 7, PS 407 10A R XTR S7-400 power supply Wide range, 120/230 V UC, 5 V DC/10 A, for redundant use, for extended temperature range and with conformal coating
27	<a href="#">6ES7407-0RA02-0AA0</a>	SIMATIC S7-400, Power supply PS407, 20 A, wide range, UC 120/230V, 5 V DC/20 A
28	<a href="#">6ES7412-1XJ07-0AB0</a>	SIMATIC S7-400, CPU 412-1 Central processing unit with: Work memory 512 KB, (256 KB code, 256 KB data), interface MPI/DP 12 Mbit/s,
29	<a href="#">6ES7412-2EK07-0AB0</a>	SIMATIC S7-400, CPU 412-2 PN Central processing unit with: Work memory 1 MB, (0.5 MB code; 0.5 MB data) interfaces 1st interface MPI/DP 12 Mbit/s, (X1), 2nd interface Ethernet/PROFINET (X5)
30	<a href="#">6ES7412-2XK07-0AB0</a>	SIMATIC S7-400, CPU 412-2 Central processing unit with: Work memory 1 MB, (0.5 MB code; 0.5 MB data) 1st interface MPI/DP 12 Mbit/s, 2nd interface PROFIBUS DP,
31	<a href="#">6ES7412-5HK06-0AB0</a>	SIMATIC S7-400H, CPU 412-5H, central processing unit for S7-400H and S7-400F/FH, 5 interfaces: 1x MPI/DP, 1x DP, 1x PN and 2 for sync modules, 1 MB memory (512 KB data/512 KB program)
32	<a href="#">6ES7414-2XL07-0AB0</a>	SIMATIC S7-400, CPU 414-2 Central processing unit with: Work memory 2 MB, (1 MB code, 1 MB data), 1st interface MPI/DP 12 Mbit/s, 2nd interface PROFIBUS DP,
33	<a href="#">6ES7414-3EM07-0AB0</a>	SIMATIC S7-400, CPU 414-3 PN/DP Central processing unit with: Work memory 4 MB, (2 MB code, 2 MB data), interfaces 1st interface MPI/DP 12 Mbit/s, (X1), 2nd interface Ethernet/PROFINET (X5) 3rd interface IF 964-DP plug-in (IF1)
34	<a href="#">6ES7414-3FM07-0AB0</a>	SIMATIC S7-400, CPU414F-3 PN/DP Central processing unit with: Work memory 4 MB, (2 MB code, 2 MB data), interfaces 1st interface MPI/DP 12 Mbit/s, (X1), 2nd interface Ethernet/PROFINET (X5) 3rd interface IF 964-DP plug-in (IF1)
35	<a href="#">6ES7414-3XM07-0AB0</a>	SIMATIC S7-400, CPU 414-3 Central processing unit with: Work memory 4 MB, (2 MB code, 2 MB data), 1st interface MPI/DP 12 Mbit/s, 2nd interface PROFIBUS DP, 3rd interface plug-in IFM module
36	<a href="#">6ES7414-5HM06-0AB0</a>	SIMATIC S7-400H, CPU 414-5H, central processing unit for S7-400H and S7-400F/FH, 5 interfaces: 1x MPI/DP, 1x DP, 1x PN and 2 for sync modules, 4 MB memory (2 MB data/2 MB program),
37	<a href="#">6ES7416-2FP07-0AB0</a>	SIMATIC S7-400, CPU 416F-2, Central processing unit with: Work memory 8 MB, (4 MB code, 4 MB data), 1st interface MPI/DP 12 Mbit/s, 2nd interface PROFIBUS DP,
38	<a href="#">6ES7416-2XP07-0AB0</a>	SIMATIC S7-400, CPU 416-2, Central processing unit with: Work memory 8 MB, (4 MB code, 4 MB data), 1st interface MPI/DP 12 Mbit/s, 2nd interface PROFIBUS DP,
39	<a href="#">6ES7416-3ES07-0AB0</a>	SIMATIC S7-400, CPU 416-3 PN/DP Central processing unit with: Work memory 16 MB, (8 MB code, 8 MB data), interfaces 1st interface MPI/DP 12 Mbit/s, (X1), 2nd interface Ethernet/PROFINET (X5) 3rd interface IF 964-DP plug-in (IF1)
40	<a href="#">6ES7416-3FS07-0AB0</a>	SIMATIC S7-400, CPU416F-3 PN/DP Central processing unit with: Work memory 16 MB, (8 MB code, 8 MB data), interfaces 1st interface MPI/DP 12 Mbit/s, (X1), 2nd interface Ethernet/PROFINET (X5) 3rd interface IF 964-DP plug-in (IF1)
41	<a href="#">6ES7416-3XS07-0AB0</a>	SIMATIC S7-400, CPU 416-3, Central processing unit with: Work memory 16 MB, (8 MB code, 8 MB data), 1st interface MPI/DP 12 Mbit/s, 2nd interface PROFIBUS DP, 3rd interface plug-in IFM module
42	<a href="#">6ES7416-5HS06-0AB0</a>	SIMATIC S7-400H, CPU 416-5H, central processing unit for S7-400H and S7-400F/FH, 5 interfaces: 1x MPI/DP, 1x DP, 1x PN and 2 for sync modules, 16 MB memory (10 MB data/6 MB program)
43	<a href="#">6ES7417-4XT07-0AB0</a>	SIMATIC S7-400, CPU 417-4 Central processing unit with: Work memory 32 MB, (16 MB code; 16 MB data) 1st interface MPI 12 Mbit/s; 2nd interface PROFIBUS DP, 3rd/4th interface plug-in IFM module

44	<a href="#">6ES7417-5HT06-0AB0</a>	SIMATIC S7-400H, CPU 417-5H, central processing unit for S7-400H and S7-400F/FH, 5 interfaces: 1x MPI/DP, 1x DP, 1x PN and 2 for sync modules, 32 MB memory (16 MB data/16 MB program)
45	<a href="#">6ES7461-0AA00-7AA0</a>	SIMATIC S7-400, terminating connector for receiver IM 461-0
46	<a href="#">6ES7461-0AA01-0AA0</a>	SIMATIC S7-400, interface module receiver IM 461-0 for central coupling without for PS transfer, with C-bus
47	<a href="#">6ES7461-1BA01-0AA0</a>	SIMATIC S7-400, interface module receiver IM 461-1 for central coupling with PS transfer, without C bus,
48	<a href="#">6ES7952-0AF00-0AA0</a>	SIMATIC S7, RAM Memory Card for S7-400, long design, 64 Kbyte
49	<a href="#">6ES7952-0KF00-0AA0</a>	SIMATIC S7, memory card for S7-400, long design, 5V Flash EPROM, 64 Kbyte
50	<a href="#">6ES7952-0KH00-0AA0</a>	SIMATIC S7, memory card for S7-400, long design, 5V Flash EPROM, 256 Kbyte
51	<a href="#">6ES7952-1AH00-0AA0</a>	SIMATIC S7, RAM Memory Card for S7-400, long design, 256 Kbyte
52	<a href="#">6ES7952-1AK00-0AA0</a>	SIMATIC S7, RAM Memory Card for S7-400, long design, 1 Mbyte
53	<a href="#">6ES7952-1AL00-0AA0</a>	SIMATIC S7, RAM Memory Card for S7-400, long design, 2 Mbyte
54	<a href="#">6ES7952-1AM00-0AA0</a>	SIMATIC S7, RAM Memory Card for S7-400, long design, 4 Mbytes
55	<a href="#">6ES7952-1AP00-0AA0</a>	SIMATIC S7, RAM Memory Card for S7-400, long design, 8 Mbyte
56	<a href="#">6ES7952-1AS00-0AA0</a>	SIMATIC S7, RAM Memory Card for S7-400, long design, 16 Mbyte
57	<a href="#">6ES7952-1AY00-0AA0</a>	SIMATIC S7, RAM Memory Card for S7-400, long design, 64 Mbyte
58	<a href="#">6ES7952-1KK00-0AA0</a>	SIMATIC S7, memory card for S7-400, long design, 5V Flash EPROM, 1 Mbyte
59	<a href="#">6ES7952-1KL00-0AA0</a>	SIMATIC S7, memory card for S7-400, long design, 5V Flash EPROM, 2 Mbyte
60	<a href="#">6ES7952-1KM00-0AA0</a>	SIMATIC S7, memory card for S7-400, long design, 5V Flash EPROM, 4 Mbytes
61	<a href="#">6ES7952-1KP00-0AA0</a>	SIMATIC S7, memory card for S7-400, long design, 5V Flash EPROM, 8 Mbyte
62	<a href="#">6ES7952-1KS00-0AA0</a>	SIMATIC S7, memory card for S7-400, long design, 5V Flash EPROM, 16 Mbyte
63	<a href="#">6ES7952-1KT00-0AA0</a>	SIMATIC S7, memory card for S7-400, long design, 5V Flash EPROM, 32 Mbyte
64	<a href="#">6ES7952-1KY00-0AA0</a>	SIMATIC S7, memory card for S7-400, long design, 5V Flash EPROM, 64 Mbyte