

Lista de precios de protección para base instalada DI PA AE PRO (PCS 7) FY'22
Vigencia de precios de febrero 15 hasta el 30 de agosto del año 2022.

No.	MLFB	Descripción
1	6ES7400-1JA01-0AA0	SIMATIC S7-400, rack UR2, central and distributed with 9 slots, 2 redundant PS can be plugged in
2	6ES7400-1JA11-0AA0	SIMATIC S7-400, rack aluminum UR2, central and distributed with 9 slots, 2 redundant PS can be plugged in
3	6ES7400-1JA11-0AA1	SIMATIC PCS 7, UR2 XTR S7-400 rack central and distributed with 9 slots, 2 redundant PS can be plugged in for extended temperature range and with conformal coating
4	6ES7400-1TA01-0AA0	SIMATIC S7-400, rack UR1, central and distributed with 18 slots, 2 redundant PS can be plugged in
5	6ES7400-1TA11-0AA0	SIMATIC S7-400, rack UR1 Alu, central and distributed with 18 slots, 2 redundant PS can be plugged in
6	6ES7400-2JA00-0AA0	SIMATIC S7-400H, rack UR2-H, central and distributed with 2 x 9 slots,
7	6ES7400-2JA10-0AA0	SIMATIC S7-400, rack aluminum UR2-H, central and distributed with 2 x 9 slots
8	6ES7400-2JA10-0AA1	SIMATIC PCS 7-400, UR2-H XTR S7-400 rack central and distributed with 2 x 9 slots, 2 x 2 redundant PS can be plugged in for extended temperature range and with conformal coating
9	6ES7401-1DA01-0AA0	SIMATIC S7-400, rack CR3, central with 4 slots
10	6ES7401-1DA01-0AA1	SIMATIC PCS 7, CR3 XTR S7-400 rack central with 4 slots for extended temperature range and with conformal coating
11	6ES7401-2TA01-0AA0	SIMATIC S7-400, rack CR2, central, 18 slots, 2 segments 2 redundant PS can be plugged in
12	6ES7403-1JA01-0AA0	SIMATIC S7-400, extension rack ER2 with 9 slots, only for signal modules 2 redundant PS can be plugged in
13	6ES7403-1JA11-0AA0	SIMATIC S7-400, extended rack ER2 aluminum, with 9 slots, for signal modules, 2 redundant PS can be plugged in
14	6ES7403-1TA01-0AA0	SIMATIC S7-400, extension rack ER1 with 18 slots, only for signal modules 2 redundant PS can be plugged in
15	6ES7403-1TA11-0AA0	SIMATIC S7-400, ext. rack ER1 aluminum, with 18 slots, for signal modules, 2 redundant PS can be plugged in
16	6ES7405-0DA02-0AA0	SIMATIC S7-400, power supply PS 405: 4 A, 24/48/60 V DC, 5 V DC/4 A,
17	6ES7405-0DA02-0AA1	SIMATIC PCS 7, PS 405 4A XTR S7-400 power supply Wide range, 24/48/60 V DC; 5 V DC/4 A, ATEX approbation identifier for extended temperature range and with conformal coating
18	6ES7405-0KA02-0AA0	SIMATIC S7-400, Power supply PS405, wide range 10 A, 24/48/60 V DC; 5 V DC/10 A ATEX approval marking
19	6ES7405-0KR02-0AA0	SIMATIC S7-400, power supply PS405: 10 A, wide range, 24/48/60 V DC; 5 V DC/10 A, for redundant use
20	6ES7405-0KR02-0AA1	SIMATIC PCS 7, PS 405 10A R XTR S7-400 power supply Wide range, 24/48/60 V DC; 5 V DC/10 A, for redundant use, ATEX approbation identifier for extended temperature range and with conformal coating
21	6ES7405-0RA02-0AA0	SIMATIC S7-400, Power supply PS405: 20 A, wide range, 24/48/60 V DC, 5 V DC/20 A, ATEX approval marking
22	6ES7407-0DA02-0AA0	SIMATIC S7-400, Power supply PS407: 4 A, wide range, UC 120/230V, 5 V DC/4 A
23	6ES7407-0DA02-0AA1	SIMATIC PCS 7, PS 407 4A XTR S7-400 power supply Wide range, 120/230 V UC; 5 V DC/4 A, for extended temperature range and with conformal coating
24	6ES7407-0KA02-0AA0	SIMATIC S7-400, Power supply PS407: 10 A, wide range, UC 120/230V, 5 V DC/10 A
25	6ES7407-0KR02-0AA0	SIMATIC S7-400, Power supply PS407; 10 A, wide range, UC 120/230V, 5 V DC/10 A, for redundant use
26	6ES7407-0KR02-0AA1	SIMATIC PCS 7, PS 407 10A R XTR S7-400 power supply Wide range, 120/230 V UC, 5 V DC/10 A, for redundant use, for extended temperature range and with conformal coating
27	6ES7407-0RA02-0AA0	SIMATIC S7-400, Power supply PS407, 20 A, wide range, UC 120/230V, 5 V DC/20 A
28	6ES7412-1XJ07-0AB0	SIMATIC S7-400, CPU 412-1 Central processing unit with: Work memory 512 KB, (256 KB code, 256 KB data), interface MPI/DP 12 Mbit/s,
29	6ES7412-2EK07-0AB0	SIMATIC S7-400, CPU 412-2 PN Central processing unit with: Work memory 1 MB, (0.5 MB code; 0.5 MB data) interfaces 1st interface MPI/DP 12 Mbit/s, (X1), 2nd interface Ethernet/PROFINET (X5)
30	6ES7412-2XK07-0AB0	SIMATIC S7-400, CPU 412-2 Central processing unit with: Work memory 1 MB, (0.5 MB code; 0.5 MB data) 1st interface MPI/DP 12 Mbit/s, 2nd interface PROFIBUS DP,
31	6ES7412-5HK06-0AB0	SIMATIC S7-400H, CPU 412-5H, central processing unit for S7-400H and S7-400F/FH, 5 interfaces: 1x MPI/DP, 1x DP, 1x PN and 2 for sync modules, 1 MB memory (512 KB data/512 KB program)
32	6ES7414-2XL07-0AB0	SIMATIC S7-400, CPU 414-2 Central processing unit with: Work memory 2 MB, (1 MB code, 1 MB data), 1st interface MPI/DP 12 Mbit/s, 2nd interface PROFIBUS DP,
33	6ES7414-3EM07-0AB0	SIMATIC S7-400, CPU 414-3 PN/DP Central processing unit with: Work memory 4 MB, (2 MB code, 2 MB data), interfaces 1st interface MPI/DP 12 Mbit/s, (X1), 2nd interface Ethernet/PROFINET (X5) 3rd interface IF 964-DP plug-in (IF1)
34	6ES7414-3FM07-0AB0	SIMATIC S7-400, CPU414F-3 PN/DP Central processing unit with: Work memory 4 MB, (2 MB code, 2 MB data), interfaces 1st interface MPI/DP 12 Mbit/s, (X1), 2nd interface Ethernet/PROFINET (X5) 3rd interface IF 964-DP plug-in (IF1)
35	6ES7414-3XM07-0AB0	SIMATIC S7-400, CPU 414-3 Central processing unit with: Work memory 4 MB, (2 MB code, 2 MB data), 1st interface MPI/DP 12 Mbit/s, 2nd interface PROFIBUS DP, 3rd interface plug-in IFM module
36	6ES7414-5HM06-0AB0	SIMATIC S7-400H, CPU 414-5H, central processing unit for S7-400H and S7-400F/FH, 5 interfaces: 1x MPI/DP, 1x DP, 1x PN and 2 for sync modules, 4 MB memory (2 MB data/2 MB program),
37	6ES7416-2FP07-0AB0	SIMATIC S7-400, CPU 416F-2, Central processing unit with: Work memory 8 MB, (4 MB code, 4 MB data), 1st interface MPI/DP 12 Mbit/s, 2nd interface PROFIBUS DP,
38	6ES7416-2XP07-0AB0	SIMATIC S7-400, CPU 416-2, Central processing unit with: Work memory 8 MB, (4 MB code, 4 MB data), 1st interface MPI/DP 12 Mbit/s, 2nd interface PROFIBUS DP,
39	6ES7416-3ES07-0AB0	SIMATIC S7-400, CPU 416-3 PN/DP Central processing unit with: Work memory 16 MB, (8 MB code, 8 MB data), interfaces 1st interface MPI/DP 12 Mbit/s, (X1), 2nd interface Ethernet/PROFINET (X5) 3rd interface IF 964-DP plug-in (IF1)
40	6ES7416-3FS07-0AB0	SIMATIC S7-400, CPU416F-3 PN/DP Central processing unit with: Work memory 16 MB, (8 MB code, 8 MB data), interfaces 1st interface MPI/DP 12 Mbit/s, (X1), 2nd interface Ethernet/PROFINET (X5) 3rd interface IF 964-DP plug-in (IF1)
41	6ES7416-3XS07-0AB0	SIMATIC S7-400, CPU 416-3, Central processing unit with: Work memory 16 MB, (8 MB code, 8 MB data), 1st interface MPI/DP 12 Mbit/s, 2nd interface PROFIBUS DP, 3rd interface plug-in IFM module
42	6ES7416-5HS06-0AB0	SIMATIC S7-400H, CPU 416-5H, central processing unit for S7-400H and S7-400F/FH, 5 interfaces: 1x MPI/DP, 1x DP, 1x PN and 2 for sync modules, 16 MB memory (10 MB data/6 MB program)
43	6ES7417-4XT07-0AB0	SIMATIC S7-400, CPU 417-4 Central processing unit with: Work memory 32 MB, (16 MB code; 16 MB data) 1st interface MPI 12 Mbit/s; 2nd interface PROFIBUS DP, 3rd/4th interface plug-in IFM module

44	6ES7417-5HT06-0AB0	SIMATIC S7-400H, CPU 417-5H, central processing unit for S7-400H and S7-400F/FH, 5 interfaces: 1x MPI/DP, 1x DP, 1x PN and 2 for sync modules, 32 MB memory (16 MB data/16 MB program)
45	6ES7461-0AA00-7AA0	SIMATIC S7-400, terminating connector for receiver IM 461-0
46	6ES7461-0AA01-0AA0	SIMATIC S7-400, interface module receiver IM 461-0 for central coupling without for PS transfer, with C-bus
47	6ES7461-1BA01-0AA0	SIMATIC S7-400, interface module receiver IM 461-1 for central coupling with PS transfer, without C bus,
48	6ES7952-0AF00-0AA0	SIMATIC S7, RAM Memory Card for S7-400, long design, 64 Kbyte
49	6ES7952-0KF00-0AA0	SIMATIC S7, memory card for S7-400, long design, 5V Flash EPROM, 64 Kbyte
50	6ES7952-0KH00-0AA0	SIMATIC S7, memory card for S7-400, long design, 5V Flash EPROM, 256 Kbyte
51	6ES7952-1AH00-0AA0	SIMATIC S7, RAM Memory Card for S7-400, long design, 256 Kbyte
52	6ES7952-1AK00-0AA0	SIMATIC S7, RAM Memory Card for S7-400, long design, 1 Mbyte
53	6ES7952-1AL00-0AA0	SIMATIC S7, RAM Memory Card for S7-400, long design, 2 Mbyte
54	6ES7952-1AM00-0AA0	SIMATIC S7, RAM Memory Card for S7-400, long design, 4 Mbytes
55	6ES7952-1AP00-0AA0	SIMATIC S7, RAM Memory Card for S7-400, long design, 8 Mbyte
56	6ES7952-1AS00-0AA0	SIMATIC S7, RAM Memory Card for S7-400, long design, 16 Mbyte
57	6ES7952-1AY00-0AA0	SIMATIC S7, RAM Memory Card for S7-400, long design, 64 Mbyte
58	6ES7952-1KK00-0AA0	SIMATIC S7, memory card for S7-400, long design, 5V Flash EPROM, 1 Mbyte
59	6ES7952-1KL00-0AA0	SIMATIC S7, memory card for S7-400, long design, 5V Flash EPROM, 2 Mbyte
60	6ES7952-1KM00-0AA0	SIMATIC S7, memory card for S7-400, long design, 5V Flash EPROM, 4 Mbytes
61	6ES7952-1KP00-0AA0	SIMATIC S7, memory card for S7-400, long design, 5V Flash EPROM, 8 Mbyte
62	6ES7952-1KS00-0AA0	SIMATIC S7, memory card for S7-400, long design, 5V Flash EPROM, 16 Mbyte
63	6ES7952-1KT00-0AA0	SIMATIC S7, memory card for S7-400, long design, 5V Flash EPROM, 32 Mbyte
64	6ES7952-1KY00-0AA0	SIMATIC S7, memory card for S7-400, long design, 5V Flash EPROM, 64 Mbyte