


The image displays a collection of Siemens 3TS Converter duty contactors, which are industrial electrical components used for switching power in converter applications. They are shown in various sizes and configurations, arranged in a cluster. Each unit features a black plastic housing with a light blue top cover. The top cover has technical specifications and terminal markings. The contactors have multiple main terminals (L1, L2, L3) and auxiliary terminals (T1, T2, T3). Some units have additional wiring and components attached to them.

SIEMENS

Ingenuity for life

3TS Converter duty contactor

Smart. Easy. Reliable.

www.siemens.co.in

Overview:

For more than 125 years, Siemens has been developing and manufacturing industrial control products. We offer a wide product range which caters to fulfill the demand of our esteemed customers with satisfactory performance level and improved reliability.

Use of power electronics is on the rise across all industries, be it renewables, heavy industries or conventional machines. With advent of digitalization, need for secure power via USP has gained significance. Converters used in these systems play an important role in the way we control and manage power.

Safety of man and machine demands proper remote or local isolation of the system and this can be catered with Siemens robust offering in control products. Our vast experience in drives and power electronics enabled us to design a perfect solution; Siemens 3TS converter duty contactors.



Range:

- 100 to 630A AC-1 at 415V AC
- Coil: 110V, 230V AC 50Hz, 24V DC

Application:

3TS Converter duty contactors can be widely used in:

VFD, Soft Starters applications

UPS

Solar and Wind inverters

Resistive loads

Battery charging

Standards:

- IEC 60947-4-1

Approbations:

- CE marking

Features:

- Offer one of the highest AC-1 rating in given size
- Arc chamber interlock
- SIGUT Termination technique
- Compact Dimensions
- Screw mounting
- Double break parallel bridge auxiliary contacts

Benefits:

- Ease of wiring (can obviate use of lugs)
- Operator Safety (contactor cannot be switched-on if arc chamber is not fitted properly)
- Space saving
- Flexible mounting
- Unmatched contact reliability (ensures reliable contact at low voltage & low currents)



Technical specifications:

Contactor Type			3TS48	3TS50	3TS51	3TS52	3TS53	3TS54	3TS55	3TS56	3TS57
Size			3	4	6	6	8	8	10	12	12
Conformance to			IEC 60947-4-1								
Number of Power Contacts			3								
Number of Auxilliary Contacts			2NO+2NC								
Permissible Ambient Temperature											
	Storage	°C	-55 to +80								
	Service ²⁾	°C	-25 to +50								
Maximum operational voltage		V	690								
Rated Insulation Voltage U_i (At Pollution Degree. 3) ¹⁾		V	1000								
Rated Impulse Strength U_{imp} (Main Circuit)		kV	8								
Mechanical endurance (Make/Break Operations)	AC	Cycles	10 x 10 ⁶								
	DC	Cycles	3 x 10 ⁶								
AC-1 duty Rated Operational Current I_e at 40°C upto 415V		A	100	145	200	225	275	325	400	525	630
Switching frequency (Contactors without overload relay)		Operation									
No-load	AC	Cycles/hr	5000	5000	5000	5000	5000	5000	3000	3000	2000
	DC	Cycles/hr	1000	1000	1000	1000	1000	1000	1000	1000	1000
	at AC-1	Cycles/hr	300	300	300	300	300	300	300	300	300
Coil Parameters		Voltages available	Uc	110V AC and 230V AC, 50Hz and 24V DC ³⁾							
AC operation 50Hz	Pick-up	VA	155	296	443		765		1440	2200	850
	Hold-on	VA	18	28.5	39.8		61.8		93.6	108	30.7
DC operation	Pick-up	W	330	312	412	16.5	739 ²⁾		951 ²⁾	1020 ²⁾	882 ²⁾
	Hold-on	W	2.2	2.74	2.97	6.22	11.0 ²⁾		13.4 ²⁾	13.7 ²⁾	22.7 ²⁾
Limits of operation		AC	0.8 to 1.1 x U_s								
		DC	0.8 to 1.2 x U_s								
Operating times at 1 x U_s											
AC Operation	Closing	ms	17-30	22-35	22-37		25-50		25-40	25-40	48-70
	Opening	ms	5-25	5-30	8-30		10-30		10-30	8-30	80-100
DC Operation	Closing	ms	22-40	32-40	28-32		32-45		36-45	40-55	44-60
	Opening	ms	105-115	95-105	185-195		10-20		10-20	10-20	12-15
Conductor cross-sections											
Main conductor											
Finely stranded with cable lug		mm ²	10 to 35	35 to 95	35 to 95	35 to 95	50 to 240	50 to 240	50 to 240	50 to 240	50 to 240
Terminal bar (max. width)		mm	12	15	20	20	25	25	25	25	30
Solid or stranded		AWG	7 to 1/0								
Tightening torque		Nm	4 to 6	10 to 14	10 to 14	10 to 14	14 to 24	14 to 24	14 to 24	14 to 24	14 to 24
Auxiliary Conductor											
Solid		mm ²	2 x (0.5 to 1, 1 to 2.5), 1 x 4								
Finely stranded with end sleeve		mm ²	2 x (0.75 to 2.5)								
Pin end connector		mm ²	1 x (1 to 1.5)								
Solid or Stranded		AWG	2 x (18 to 12)								
Tightening torque		Nm	0.8 to 1.4								

1) As per IS/IEC 60947-1

2) Include switching contactor

3) 24V DC coil variant not available for 3TS57

Selection and ordering data:

Converter duty contactors - 3TS

Contactor size	Rated current I _e (A) AC1 at 415V	AC Coil ¹⁾	DC Coil ¹⁾
3	100	3TS48 22-0A.. 1-8K	3TS48 22-0D.. 1-8K
4	145	3TS49 22-0A.. 1-8K	3TS49 22-0D.. 1-8K
6	200	3TS51 22-0A.. 1-8K	3TS51 22-0D.. 1-8K
6	225	3TS52 22-0A.. 1-8K	3TS52 22-0D.. 1-8K
8	275	3TS53 22-0A.. 1-8K	3TS53 22-0D.. 1-8K
8	325	3TS54 22-0A.. 1-8K	3TS54 22-0D.. 1-8K
10	400	3TS55 22-0A.. 1-8K	3TS55 22-0D.. 1-8K
12	525	3TS56 22-0A.. 1-8K	3TS56 22-0D.. 1-8K
12	630	3TS57 22-0C.. 1-8K	

Coil voltages for 3TS48 - 3TS56

	AC Coil (50Hz)		DC Coil
Code	F0	P0	B4
Coil voltages	110	230	24

Coil voltages for 3TS57

AC 50/60Hz	Coil voltage (V)	110-132	220-240
	Code	F7	M7

Spare coils


Contactor rating	AC Coil	DC Coil
3TS48	3TY7 463-0A..	3TY7 463-0D..
3TS50	3TY7 483-0A..	3TY7 483-0D..
3TS51/52	3TY7 503-0A..	3TY7 503-0D..
3TS53/54	3TY7 523-0A..	3TY7 523-0D..
3TS55	3TY7 543-0A..	3TY7 543-0D..
3TS56	3TY7 563-0A..	3TY7 563-0D..
3TS57	3TY7 573-0C..	

Main contact kits (set of 6 fixed & 3 moving contacts)


Contactor rating	Description	MLFB
3TS48	Spare main contact kits	3TS91 48-01-8K
3TS50		3TS91 50-01-8K
3TS51		3TS91 51-01-8K
3TS52		3TS91 52-01-8K
3TS53		3TS91 53-01-8K
3TS54		3TS91 54-01-8K
3TS55		3TS91 55-01-8K
3TS56		3TS91 56-01-8K
3TS57		3TS91 57-01-8K



Mounting details:




Terminal drawing:




Dimensional drawing:

3TS AC-1 Contactors



Type	Contactor Dimensions						Drilling Plan		
	W	W1	H	H1	D	D1	DW	DH	Ød
3TS48...1-8K	90	113	117	94	123	80	70	100	4.8
3TS50...1-8K	100	123	133	123	140	89	80	110	5.5
3TS51...1-8K	120	143	150	139	154	93	100	130	6.3
3TS52...1-8K	120	143	150	139	154	93	100	130	6.3
3TS53...1-8K	135	158	180	159	188	115	110	160	7
3TS54...1-8K	135	158	180	159	188	115	110	160	7
3TS55...1-8K	150	168	205	168	201	132	120	180	9
3TS56...1-8K	160	183	200	182	222	150	130	180	9
3TS57...1-8K	160	183	210.5	182	222	150	130	180	9

Note: Minimum clearance from insulated components, C = 3mm
Minimum clearance from earthed components, C = 10mm



Your partners

Sales offices:

Ahmedabad
3rd Floor, Prerna Arbour
Girish Coldrinks Cross Roads, Navrangpura
Ahmedabad - 380 009
☎ : +91 79 30927600
Fax: +91 79 30927699

Baroda
Ground Floor, Urja Bhavan
Opp.Makarpura Railway Station, Maneja
Vadodara - 390 013
☎ : +91 265 3957701
Fax: +91 265 3039190

Bengaluru
1st Floor, Jyoti Mahal, No. 49, St. Marks Rd.
Bengaluru - 560 001
☎ : +91 80 33422000
Fax: +91 80 33424131

Chandigarh
SCO 188/191, 3rd Floor, Sector-17 C
Chandigarh - 160 017
☎ : +91 172 4690300
Fax: +91 172 4690399

Territory managers:

Agra
31, Maitri Bagh, Dayal Bagh
Agra - 282005, UP
Mobile: +91 7619047999
E-mail: achint.mathur@siemens.com

Angul
Flat No. 209, Block - B, 2nd Floor
OM Residency, Gandhi Marg
Infront of Kalyani Narsingh Home
Angul, Odisha - 759122
Mobile: +91 9437114662
E-mail: sudipta.garnayak@siemens.com

Aurangabad
Flat No. 603, Building A2
Disha Sanskruti Silkcity, Palthan Road
Aurangabad - 431001 (MH)
Mobile: +91 7720032974
E-mail: Prashant.Joshi@siemens.com

Belgaum
H.No.713, Narvekar Lane, Shahpur
Belgaum - 590003, Karnataka
Tel.: +91 0831 2495156
Mobile: +91 9740277991
E-mail: anand.gawade@siemens.com

Belgaum
Flat No. 7, 2nd Floor, Jyotirling Plaza
Congress Road, Thilakwadi
Belgaum - 590011, Karnataka
Mobile: +91 7259400100
E-mail: prathish.t_m@siemens.com

Bharuch
Gold B, 804, Samruddhi Residency
Opp.Zadeshwar Bus Stop, Zadeshwar Road
Bharuch - 392011
Mobile: +91 9429037805
E-mail: kalpeshkumar.darji@siemens.com

Bhilai
Clo. Mr. Anil Dhusia, Qtr No. 4A, Street 33
Sector - 4, Bhilai - 490001
Mobile: +91 7869922211
E-mail: pravin.deshbhtrata@siemens.com

Bhopal
Flat No. 104, Sagor Home Phase-2
Sarvadiharma Society, Sector A
Nayapura Road
Bhopal - 462042, Madhya Pradesh
Mobile: +91 9977228084
E-mail: prajwal.khapekar@siemens.com

Bhubaneswar
104 Sector 5, Niladri Vihar, Chandrasekharapur
Bhubaneswar, Odisha - 751021
Mobile: +91 7399638488
E-mail: ravi.modi@siemens.com

Bhubaneswar
Plot No. 233, Shahid Nagar
Bhubaneswar - 751007
Mobile: +91 7894436373
E-mail: somnath.manna@siemens.com

Bhubaneswar
Plot No. 486, Flat No. 302
Archid Royal Apartment, Nageswar Tangi
Bhubaneswar - 751002, Odisha
Mobile: +91 9040001343
E-mail: pm.barik@siemens.com

Boisar
Flat No. A-21, Sai Sagar CHS
MAHADRA Colony, Chitrayalaya Road
Boisar - 401506
Mobile: +91 9819231892
E-mail: debashis.biswas@siemens.com

Cochin
K.G.Oxford Business Centre
3A, Shreeekandath Rd., Ravipuram
Cochin - 682016
Tel.: +91 4028611222
Mobile: +91 9846006580
E-mail: girish.v_nair@siemens.com

Cochin
K.G.Oxford Business Centre
3A, Shreeekandath Road, Ravipuram
Cochin - 682016
Mobile: +91 9526065551
E-mail: abhishek.tyagi@siemens.com

Chennai
4th Floor, ETA Mount Central
Seethakathi Business Centre, Mount Road
Chennai - 600006
☎ : +91 44 30474000
Fax: +91 44 30474080

Coimbatore
1st Floor, "Senthil Towers"
1078, Avinashi Road
Coimbatore - 641018
☎ : +91 422 3076300
Fax: +91 422 3076310

Gurgaon
Plot No. - 78, Tower - B
Jagatjit Industries Building (JIL)
Opposite SBI Academy, Sector-18
Gurgaon - 122015
☎ : +91 124 2842000, 3810200

Cochin
K.G.Oxford Business Centre
3A, Shreeekandath Road, Ravipuram
Cochin - 682016
Mobile: +91 9656690111
E-mail: vinu.pillai@siemens.com

Durg
Plot No. 18 Anand Vihar Phase-1
Borsi South, Durg - 491001, (CG)
Mobile: +91 9425016197
E-mail: jitendra.potdar@siemens.com

Durgapur
6/15, Bengal Ambuja
(Near Durgapur Cinema Hall), Citi Centre
Durgapur - 713216
Mobile: +91 9051020207
E-mail: sayantan.ghosh@siemens.com

Gandhidham
Plot No. 299, Ward 3A, Adipur
Gandhidham - 370205, Gujarat
Mobile: +91 9099010323
E-mail: Vismay.pandya@siemens.com

Goa
House No. S-2, Classicue Appartment
Porvrim, Goa - 403501
Mobile: +91 7722008113
E-mail: jitih.jacob@siemens.com

Gulbarga
Flat No.13, 3rd Floor, Shubha Residence
Deshmukh Layout, Drajmapur, Kalaburagi
Gulbarga District - 585103 Karnataka
Mobile: +91 7259661717
E-mail: anirudh.ganta@siemens.com

Guwahati
H.No. 20, Ushanagar, Dispur Supermarket
Guwahati - 781006, Assam, India
Mobile: +91 9874484442
E-mail: subhajyoti_majumder@siemens.com

Guwahati
H.No. 20, Ushanagar, Dispur Supermarket
Guwahati - 781006, Assam, India
Mobile: +91 9903200417
E-mail: Amitava.Mondal@siemens.com

Haridwar
Plot No. 3B, House No. 229/30
Deep Ganga Apartments, Sector-5A, SIDCUL
Haridwar - 249403, UP
Mobile: +919839102434
E-mail: shagun.gupta@siemens.com

Hospet
Ramanand Residency, Flat No. 204
1st Main, Nehru Co-op Colony
Hospet - 583203, Karnataka
Mobile: +91 9901400227
E-mail: roy.sanjib@siemens.com

Hospet
Mahima's, Door No.1288, 9th Ward
Near Markendeshwara School
M.P.Prakash Nagar
Hospet - 583201 Distt Bellary, Karnataka
Mobile: +91 9945859004
E-mail: nagaraj.rk@siemens.com

Hospet
727, Lakshmi Narasimha Nilaya
Near Surbhi Kalyana Mantapa
Amaravathi, Hospet - 583203
Mobile: +91 9741114877
E-mail: naveen.sn@siemens.com

Hosur
B2, "Sunshine" 1st Floor
Sipcot Housing Colony, Dharga
Hosur - 635126, Tamilnadu
Mobile: +91 9880213880
E-mail: kamalanaban.tv@siemens.com

Hubli
21, Sri Mallikarjuna Nilaya, 1st Floor
Somanagowdara Layout, Bengeri Extension
Hubli - 580023, Karnataka
Mobile: +91 9880003724
E-mail: kr.purushottam@siemens.com

Indore
Satyemittra Rajlaxmi Nature
D-410, Near Surya Temple, R R CAT
Pithampur Road, Indore - 452012
Mobile: +91 9977236899
E-mail: raghvendra.bhadouria@siemens.com

Hyderabad
5-9-19, 4th & 5th Floor
Laxmi Narasinh Estate
Opp. Secretariat Road
Saifabad
Hyderabad - 500 004
☎ : +91 40 30922500
Fax: +91 40 30923145

Jaipur
6, Park Street
Opp. Pink City Petrol Pump
M.I.Road
Jaipur - 302 006, Rajasthan
☎ : +91 141 5152108
Fax: +91 141 2370482

Jamshedpur
"Roshan Tower"
Main Road, Bistupur (2nd Floor)
Jamshedpur - 831001
☎ : +91 657 6682201

Indore
Clo. Mr. Mahendra Nandedkar
Plot No. CH-30, Scheme No. 74, Vijay Nagar
Near Prestige Collage, Indore - 452010
Mobile: +91 9049149199
E-mail: kulkarini.shridhar@siemens.com

Jaipur
Kirtan Enclave, Flat No. 316, C Block
Jaipur Keonjhar Road, Jaipur
Odisha - 755019, Chhordha Chaak
(Nearest Land Mark - SBI ATM counter)
Mobile: +91 9937189624
E-mail: probir.mukherjee@siemens.com

Jalandhar
H.No. 140, Ground Floor, Defence Colony
Jalandhar, Punjab - 144001
Mobile: +91 8427979870
E-mail: himanshu.kaushik@siemens.com

Jammu
H.No. 1A, Sector-1 Extension
Friends Colony, Near Marble Market
Trikuta Nagar Extension, Jammu - 190012
Mobile: +91 9888851497
E-mail: chander.parkash@siemens.com

Jodhpur
D-212, Near Sai Baba Mandir
Shankar Nagar, Pal Road, Jodhpur - 342007
Mobile: +91 98508590333
E-mail: jain.nitin@siemens.com

Kanpur
Flat No.702, Pushpi Apartments
Sharda Nagar, Kanpur - 208025, UP
Mobile: +91 8650404404
E-mail: shashibhushan.prasad@siemens.com

Kolhapur
RS No. 84-1, Pinac Prasad, Fl. No. A-35
New Palace Road, Kolhapur - 416006
Mobile: +91 9850836839
E-mail: vinay.todkar@siemens.com

Kota
406, Manglayatan Appartment
Near Jain Temple, Bhimganj Mandi
Kota - 324002
Mobile: +91 9828419111
E-mail: avinash.mathur@siemens.com

Ludhiana
H.No. 1858, First Floor, Sector-32A
Ludhiana - 141008, Punjab
Mobile: +91766047929
E-mail: sunil.singla@siemens.com

Ludhiana
H.No. 728, First Floor, Sector-33,
Chandiagarh Rd., Ludhiana - 141010, Punjab
Mobile: +91 9878094677
E-mail: rohit.bhardwaj@siemens.com

Ludhiana
R-115, Near DAV School
Sarabha Nagar Extension, Phase-2
Pakhawal Road, Ludhiana, Punjab - 142022
Mobile: +91 9888484066
E-mail: padam.sharma@siemens.com

Madurai
Anirudh Block F-Top 3
Vasudhara Apartment, 84, TPK Main Road
Andalpuram, Madurai - 625 003
Tamil Nadu
Mobile: +91 9894617776
E-mail: sivaprakasam.r@siemens.com

Mangalore
Flat No. 4H55/C, Door No. 1-17/381
Derbal, Konchadi, Land Links Township
Mangalore - 575008
Mobile: +91 9980929254
E-mail: sagar.h@siemens.com

Meerut
E-205, Ansal Courtyard, Roorkee Bypass
Modipuram, Meerut - 250110, UP
Mobile: +91 9720999887
E-mail: singh.vineet@siemens.com

Meerut
C-904, Ansal Courtyard, Roorkee Bypass
Modipuram, Meerut - 250110, UP
Mobile: +91 9999702981
E-mail: shailendra.kumar@siemens.com

Kolkata
3rd Floor, 43, Shanti Palli
Rashbihari Bypass Connector
Kolkata - 700042, India
☎ : +91 33 30939000
Fax: +91 33 30939010

Lucknow
510-511, 5th Floor, Shalimar Titanium
Plot No. TC.G-1/1, Vibhuti Khand
Gomti Nagar, Lucknow
Uttar Pradesh 226010
☎ : +91 522 4031039

Mumbai
Business Centre-1
Thane Belapur Road
Thane - 400 601
☎ : +91 22 39663000
Fax: +91 22 39663721

Nashik
414, Rajdhar Bhandhu, Ghankar Lane
Ravivar Peth, Nashik - 422001
Mobile: +91 9822193204
E-mail: rushikesh.rajdhar@siemens.com

Nashik
Flat No. A-4203, Brindavan Gardens
Kedar Nagar, Shramik Nagar
Near Satpur MIDC, Nashik - 422012
Mobile: +91 9619620068
E-mail: jugal.shah@siemens.com

Neemrana
Flat No. F111, Anantraj Aashray Apartment
Plot No. 236 Japanese Zone
Neemrana - 301705, Dist.- Alwar
Mobile: +91 9650481919
E-mail: deepak.beniwal@siemens.com

Patna
Swastik Enclave, Flat No. 102
Ram Jaipal Nagar, Road No. 9, Gola Road
Bailly Road, Patna - 801503
Mobile: +91 9771414108
E-mail: vikash.prasad@siemens.co.

Pondicherry
R.A.M Paradise, II Floor, No.4, 2nd Cross
Kamban Nagar, Reddiarpalayam
Puducherry - 605010
Mobile: +91 9176609374
E-mail: gopalakrishnan.shanmugam@siemens.com

Raipur
103 Risabh Regency
Near Shri Medishine Hospital
New Rajendra Nagar Raipur(C G) - 492001
Mobile: +91 9425601849
E-mail: raghuraj.bisen@siemens.com

Rajamahendravaram
Flat No. 401, SVR Residency
77-2-29/3, Gandhipuram-3
Rajamahendravaram - 533106, A.P.
Mobile: +91 9948664228
E-mail: naga.ganesna@siemens.com

Rajkot
301, Snowhill Apartment
Near Golden Supermarket, Amin Marg
Rajkot - 360007, Gujarat
Mobile: +91 9909904993
E-mail: piyush.thaker@siemens.com

Ranchi
Flat No. A-101, 1st Floor
Sundaram Apartment, Kilburn Colony
Hinoo, Ranchi, Jharkhand - 834002
Mobile: +91 8294052647
E-mail: shyamal.bhattacharyya@siemens.com

Ranchi
2/44 New Area Gandhi Nagar
Flat Name - Lila Raj Sadhan, 2nd Floor
Hinoo, Ranchi - 834002
Mobile: +91 7766906595
E-mail: bikram.sarkar@siemens.com

Renukoot
Raj Bhawan (Near Khatu Shyam Mandir)
Awadh Colony, Murdhw, Renukoot
Sonbehadra - 231217, UP
Mobile: +91 9889384222
E-mail: umesh.pandey@siemens.com

Rourkela
D/7, Gafour Colony, Ground Floor
Near LIC Office, Udit Nagar
Rourkela - 769012, Odisha
Mobile: +91 9776967773
E-mail: prakhar.chaturvedi@siemens.com

Rourkela
N/6, Flat No. 3A, Civil Township
Opposite Hi-tech Medical College & Hospital
Rourkela, Odisha - 769004
Mobile: +91 9937972407
E-mail: shouvik.mitra@siemens.com

Rudrapur
Flat No. 202, Tower Indus 'B'
Omaxe Riviera Ltd.
Rudrapur - 263153, Uttarakhand
Mobile: +91 9918002525
E-mail: atul.shukla@siemens.com

Nagpur
5th Floor, Land Mark Building
Wardha Road, Ramdas Peth
Nagpur - 440 010
☎ : +91 712 3093000
Fax: +91 712 3093111

Pune
Tower B/701-705, ICC Trade Tower
403A, Senapati Bapat Road
Pune - 411016
☎ : +91 20 30466000
Fax: +91 20 30466060

Visakhapatnam
2nd Floor, 30-8-47
Lakshmi Narasimha Towers
Banu Street, Daba Gardens
Visakhapatnam - 530 020
Andhra Pradesh
☎ : +91 891 3050200
Fax: +91 891 3050222

Rudrapur
Flat No. 104, Tower Rhone 'C'
Omaxe Riviera Ltd.
Rudrapur - 263153, Uttarakhand
Mobile: +91 9621070111
E-mail: abhinav.rastogi@siemens.com

Salem
Rajagiragham, Lumбини Illam
No.20, Palaniappa Nagar Hasthampatti
Salem - 636007
Mobile: +91 8754922245
E-mail: g.suresh@siemens.com

Siliguri
Clo. Radhagobindo Paul
Syed Mustafa Ali Road
Raja Rammohan Roy Road, Hakimpara
Ward Number XV, Dist. Darjeeling - 741201
Mobile: +91 9932276294
E-mail: dibjoyoti.karmakar@siemens.com

Sonepat
H.No. 1103, 1st Floor, Sector-14
Sonepat, Haryana - 131001
Mobile: +91 9855526122
E-mail: kumar.manish@siemens.com

Sriperumbudur
C-32 Block, 3rd Floor, Flat No. 31
TVH svaya apartments
Near Vengadu Village, Kundrathur Road
Sriperumbudur - 602105
Mobile: +91 9884102638
E-mail: venkatesh.janakiraman@siemens.com

Surat
3/A, Navrachana Society, Opp.D.K.Park
Bharat Road, Surat - 395001
Mobile: +91 9879510191
E-mail: mitul.kapadia@siemens.com

Surat
A-604, Stuti Universal, Green City Road
Pal-Adajan, Surat - 395009, Gujarat
Mobile: +91 9712445504
E-mail: harshwardhan.mishra@siemens.com

Trichy
1/1209-B, 6th Cross Street, West Extension
Vasan Nagar, Rettai Vaikkal, Vayalur Road
Trichy - 620102
Mobile: +91 9176609375
E-mail: Muthu.kumar@siemens.com

Trivandrum
House No. 30, Ganga Nilayam
Swathy Nagar, Kazhakkuttom
Trivandrum 695582
Mobile: +91 9947957839
E-mail: nobin.babu@siemens.com

Udaipur
A-39, New Ahinsapuri, Fatehpura
Udaipur - 313004
Mobile: +91 9983691888
E-mail: anurag.shah@siemens.com

Ujjain
Tirupati Hights, B-Block, Flat No. 206
Nana Kheda, Ujjain-Indore Road
Ujjain - 456010 (MP)
Mobile: +91 8889911401
E-mail: bhadauria.amit@siemens.com

Vapi
Flat No. 201, Gayatri Building
Near Jalaram Temple, NH 8
Vapi, District Valsad - 396195
Mobile: +91 9687668690
E-mail: pandey.abhishek@siemens.com

Vapi
Shubham Tower No.3, 'C' Wing
Flat No.1006, Chala, Vapi Daman Road
Vapi, District Valsad - 396195
Mobile: +91 9825147957
E-mail: s.anand@siemens.com

Vijayawada
Laxmi Nivas, 1st Floor, Flat No. FF2
44/3 & 44/2, Plot No. 08
Sundarayya Nagar, Payakapuram
Vijayawada - 520015, Andhra Pradesh
Mobile: +91 9642351144
E-mail: venkateswar.d@siemens.com

Siemens Ltd.
Digital Factory
Control Products
R&D Technology Centre
Kalwa Works, Thane Belapur Road, Thane - 400 601
Fax: +91 22 33265627
For more information contact toll free 1800 209 1800
E-mail: lvsgr-mktg.india@siemens.com

www.siemens.co.in

DF-CP-1048-2016

Customer Care Toll free no. 1800 209 0987
Email: ics.india@siemens.com

Product upgradation is a continuous process. Hence, data in this catalog is subject to change without prior notice. For the latest information, please get in touch with our Sales Offices.