

SIEMENS

AFTERMARKET RENEWAL PARTS CATALOG

tiastar™ and legacy Motor Control Centers

usa.siemens.com/mccaftermarket






Table of contents

Aftermarket Parts Catalog


MCC Identification Guide	4
Ordering Processes	6
Industry Mall	6
COMPAS	7
Section Parts	8
Splice Kits	8
Drip Shield Kits	9
Structural Parts	10
Unit Parts	11
Auxiliary Handle Switch Kits	11
Door Assembly Kits and Door Parts	12
Handle Operating Mechanism Kits	16
MCC Control Fuse Kits	18
MCC Control Part Kits	19
MCC Terminal Blocks	19
Nameplate Kits	20
Overload Reset Kits	20
Shutter Mechanism Kits	20
Miscellaneous	21

For instruction manuals and instructional videos please see the Siemens Motor Control Center website usa.siemens.com/mcc

The data presented within this catalog is subject to change, without notice, owing to periodic updates and corrections. Please be advised that several assumptions had to be made in order to generate this and, accordingly, no representation or warranty is given with regard to its accuracy or completeness of the information as the same has been included for general purposes only and that, it should not be relied upon for any specific purpose. Siemens industry, inc. Or its affiliates, officers, employees or agents are neither responsible nor liable for inaccuracies, errors or omissions, or for any loss, damage or expense, including, without limitation, any loss of profit, indirect, special, incidental or consequential loss / damages, arising out of this data.

MCC Type Identification Guide

To identify the Siemens Motor Control Centers (MCC) model type, please refer to the MCC Identification Guide for MCC Aftermarket Renewal Parts. This document, CCBR-MCCAR-0813, is available on our website www.usa.siemens.com/mccaftermarket under the Downloads / Support section.



The screenshot shows the Siemens website's 'Aftermarket and replacement' section. It features a video player with a white circle highlighting the 'Downloads' tab. The 'Downloads' tab is expanded, showing a list of documents under the 'Catalogs' heading:

- Catalog - tiastar MCC identification guide
- Catalog - tiastar and legacy MCCs aftermarket renewal parts
- Catalog and application guide - tiastar MCC catalog and application guide

Below the video player, there is a 'Downloads' section with a 'Support' link. The 'Downloads' section is also expanded, showing a list of documents under the 'Catalogs' heading:

- Catalog - tiastar MCC identification guide
- Catalog - tiastar and legacy MCCs aftermarket renewal parts
- Catalog and application guide - tiastar MCC catalog and application guide

The 'Support' section is also expanded, showing a list of documents under the 'Installation guides' heading:

- Installation guides - General, tiastar handle mechanism kits, legacy models handle mechanism kits

1. Visit our website usa.siemens.com/mccaftermarket
2. Scroll down to Downloads / Support
3. Click on the link for "Catalog - tiastar MCC identification guide" and the document will automatically display





Use Industry Mail to order

Ordering process using Industry Mail


Step 1

Choose the required item ordering number via the MCC Aftermarket Renewal Parts Catalog.




Step 2

After logging in to Industry Mail (mall.industry.siemens.com), enter the ordering number in the Product Search.




Step 3

Enter the quantity and click add to cart.



Step 4

Add another items if desired, click on shopping cart, and proceed to checkout.



Note: If you could not find the item that you are looking for in this catalog, please call Customer Service at 1-866-663-7324.

Use COMPAS to order

Ordering process using COMPAS


Step 1

Choose the required item ordering number via the MCC Aftermarket Renewal Parts Catalog.




Step 2

After logging in to COMPAS and clicking on Manage Jobs, enter the ordering number in the Product ID box.




Step 3

Enter the quantity desired and press enter.



Step 4

Add other items if desired following the previous steps. When finished adding product, click Submit for Pricing Approval.



Note: If you could not find the item that you are looking for in this catalog, please call Customer Service at 1-866-663-7324.

Section Parts

Splice Kits

Bus splice plate(s), mounting hardware, and installation guide are included in the Splice Kit.

These section parts are only compatible with Model 95+, System 89, and tiastar structures.

50°C Horizontal Bus Silver Plated Kit Type	Ordering Number
600A	8PG1191-2KA00
800A	8PG1191-2KA01
1200A	8PG1191-2KA02
1600A	8PG1191-2KA03
2000A	8PG1191-2KA04
2500A	8PG1191-2KA05

50°C Horizontal Bus Tin Plated Kit Type	Ordering Number
600A	8PG1191-2KB00
800A	8PG1191-2KB01
1200A	8PG1191-2KB02
1600A	8PG1191-2KB03
2000A	8PG1191-2KB04
2500A	8PG1191-2KB05

Neutral Bus Kit Type	Ordering Number
600A, Silver Plated	8PG1191-2KC00
800A, Silver Plated	8PG1191-2KC01
600A, Tin Plated	8PG1191-2KC02
800A, Tin Plated	8PG1191-2KC03

Splice Kit



Ground Bus Kit Type	Ordering Number
300A, Top Mounted, Bare Copper	8PG1191-2KD00
600A, Top Mounted, Bare Copper	8PG1191-2KD01
300A, Bottom Mounted, Bare Copper	8PG1191-2KD02
600A, Bottom Mounted, Bare Copper	8PG1191-2KD03
300A, Top Mounted, Tin Plated	8PG1191-2KD04
600A, Top Mounted, Tin Plated	8PG1191-2KD05
300A, Bottom Mounted, Tin Plated	8PG1191-2KD06
600A, Bottom Mounted, Tin Plated	8PG1191-2KD07

65°C Horizontal Bus Silver Plated Kit Type	Ordering Number
600A	8PG1191-2KE00
800A	8PG1191-2KE01
1200A	8PG1191-2KE02

65°C Horizontal Bus Tin Plated Kit Type	Ordering Number
600A	8PG1191-2KF00
800A	8PG1191-2KF01
1200A	8PG1191-2KF02

Section Parts

Drip Shield Kits

Drip shield, channel, and mounting hardware are included in the Drip Shield Kit.

These section parts are only compatible with Model 95+, System 89, and tiastar structures.

15" Deep Drip Shield Kit Type	Ordering Number
20" Wide	8PG1191-1SA00
30" Wide	8PG1191-1SA01
40" Wide	8PG1191-1SA02
50" Wide (20" Left Section, 30" Right Section)	8PG1191-1SA03
50" Wide (30" Left Section, 20" Right Section)	8PG1191-1SA04
60" Wide (3, 20" Sections)	8PG1191-1SA05
60" Wide (2, 30" Sections)	8PG1191-1SA06
80" Wide	8PG1191-1SA07

20" Deep Drip Shield Kit Type	Ordering Number
20" Wide	8PG1191-1SB00
30" Wide	8PG1191-1SB01
40" Wide	8PG1191-1SB02
50" Wide (20" Left Section, 30" Right Section)	8PG1191-1SB03
50" Wide (30" Left Section, 20" Right Section)	8PG1191-1SB04
60" Wide	8PG1191-1SB05
80" Wide	8PG1191-1SB06

21" Deep Drip Shield Kit Type	Ordering Number
20" Wide	8PG1191-1SC00
30" Wide	8PG1191-1SC01
40" Wide	8PG1191-1SC02
60" Wide	8PG1191-1SC03
80" Wide	8PG1191-1SC04
50" Wide	8PG1191-1SC05

Extended Top Plates



Extended Top Plates

Extended Top Plates	Ordering Number
20" Wide Front Extended Top Plate	8PG1191-1PE00
40" Wide (20-20) Front Extended Top Plate	8PG1191-1PE01
30" Wide Front Extended Top Plate	8PG1191-1PE02
60" Wide (20-20-20) Front Extended Top Plate	8PG1191-1PE03

Section Parts

Structural Parts

Removable Bottom Plate Kits, Top Front Cover Plate Kits, Side Cover Kits, Rear Cover Plate Kits and Top Wireway Separator Kits will include assembly, mounting hardware, and installation guide (if necessary).


These section parts are only compatible with Model 95+, System 89, and tiastar structures.

Removable Bottom Plate Kit	Ordering Number
20" Wide By 15" Deep Left Hand Or Single	8PG1191-1PB00
30" Wide By 15" Deep Left Hand Or Single	8PG1191-1PB01
20" Wide By 20" Deep Left Hand Or Single	8PG1191-1PB02
30" Wide By 20" Deep Left Hand Or Single	8PG1191-1PB03
20" Wide By 21" Deep Left Hand Or Single, Back To Back	8PG1191-1PB04
30" Wide By 21" Deep Left Hand Or Single, Back To Back	8PG1191-1PB05

Top Front Cover Plate Kit	Ordering Number
20" Wide	8PG1191-1PC00
30" Wide	8PG1191-1PC01

Side Cover Kit	Ordering Number
Horizontal Bus Bar Side Cover Kit, 15" Deep	8PG1191-1PS00
Horizontal Bus Bar Side Cover Kit, 20" Deep	8PG1191-1PS01
Horizontal Bus Bar Side Cover Kit, 21" Deep, Back To Back	8PG1191-1PS02
Bottom Ground Side Cover Kit, 15" Deep	8PG1191-1PS03
Bottom Ground Side Cover Kit, 20" Deep	8PG1191-1PS04
Bottom Ground Side Cover Kit, 21" Deep, Back To Back	8PG1191-1PS05

MCC Section Drawing



- 1 = Removable Bottom Plate
- 2 = Top Front Cover Plate Kit
- 3 = Horizontal Bus Bar Side Cover Kit
- 4 = Bottom Ground Side Cover Kit
- 5 = Rear Cover Plate Kit
- 6 = Top Rear Cover Plate Kit
- 7 = Top Wireway Separator

Rear Cover Plate Kit	Ordering Number
20" Wide, 1 Piece	8PG1191-1PR00
20" Wide, 2 Piece	8PG1191-1PR01
24" Wide, 2 Piece	8PG1191-1PR02
30" Wide, 2 Piece	8PG1191-1PR03
20" Wide Top Rear Cover Plate Kit For 20" Deep Sections	8PG1191-1PR04
30" Wide Top Rear Cover Plate Kit For 20" Deep Sections	8PG1191-1PR05

Top Wireway Separator Kit	Ordering Number
20" Wide	8PG1191-1PW00
30" Wide	8PG1191-1PW01

Unit Parts

Auxiliary Handle Switch

Switch assembly, mounting hardware, and installation guide are included in the Auxiliary Handle Switch Kit.

tiastar Handle Auxiliary Switch Kit Type	Ordering Number
Form C, 300V AC, Left Side Mount (125-600A Sentron CB; 30-200A Fusible Disconnect)	8PG1192-2AA00
Form C, 300V AC, Right Side Mount (125-600A Sentron CB; 30-200A Fusible Disconnect)	8PG1192-2AA01
1NO-1NC, 600V AC, Backplate Mounted (250A Sentron CB)	8PG1192-2AA02
2NO-2NC, 600V AC, Backplate Mounted (250A Sentron CB)	8PG1192-2AA03
1NO-1NC, 600V AC, Backplate Mounted (125A Sentron CB; 30/60A Fusible Disconnect;)	8PG1192-2AA06
2NO-2NC, 600V AC, Backplate Mounted (125A Sentron CB; 30/60A Fusible Disconnect;)	8PG1192-2AA07
1NO-1NC, 600V AC, Backplate Mounted (100A Fusible Disconnect)	8PG1192-2AA08
2NO-2NC, 600V AC, Backplate Mounted (100A Fusible Disconnect)	8PG1192-2AA10
1NO-1NC, 600V AC, Backplate Mounted (400/600A Sentron CB)	8PG1192-2AA11
2NO-2NC, 600V AC, Backplate Mounted (400/600A Sentron CB)	8PG1192-2AA12

Auxiliary Handle Switch




Unit Parts

Door Assembly Kits and Door Parts—Model 95+ and System 89/tiastar

Door, hinges, and mounting hardware included in the Model 95+ and System 89/tiastar Door Assembly Kit.

Vertical Wireway Door Kit Type	Ordering Number
4" Wide By 12" Tall	8PG1192-1DD00
4" Wide By 18" Tall	8PG1192-1DD01
4" Wide By 24" Tall	8PG1192-1DD02
4" Wide By 30" Tall	8PG1192-1DD03
4" Wide By 36" Tall	8PG1192-1DD04
4" Wide By 42" Tall	8PG1192-1DD05
4" Wide By 48" Tall	8PG1192-1DD06
4" Wide By 54" Tall	8PG1192-1DD07
4" Wide By 60" Tall	8PG1192-1DD08
4" Wide By 66" Tall	8PG1192-1DD10
4" Wide By 72" Tall	8PG1192-1DD11
8" Wide By 12" Tall	8PG1192-1DD12
8" Wide By 18" Tall	8PG1192-1DD13
8" Wide By 24" Tall	8PG1192-1DD14
8" Wide By 30" Tall	8PG1192-1DD15
8" Wide By 36" Tall	8PG1192-1DD16
8" Wide By 42" Tall	8PG1192-1DD17
8" Wide By 48" Tall	8PG1192-1DD18
8" Wide By 54" Tall	8PG1192-1DD20
8" Wide By 60" Tall	8PG1192-1DD21
8" Wide By 72" Tall	8PG1192-1DD22
Top Wireway Door Kit Type	Ordering Number
20" Wide By 12"	8PG1192-1DD23
30" Wide By 12"	8PG1192-1DD24

6" Tall Filler Door Kit



Door Kit Type	Ordering Number
15" Wide By 6" Tall Filler Door	8PG1192-1DE01
15" Wide By 12" Tall Blank Door	8PG1192-1DE03
15" Wide By 18" Tall Blank Door	8PG1192-1DE04
15" Wide By 24" Tall Blank Door	8PG1192-1DE05
15" Wide By 30" Tall Blank Door	8PG1192-1DE06
15" Wide By 36" Tall Blank Door	8PG1192-1DE07
15" Wide By 42" Tall Blank Door	8PG1192-1DE08
15" Wide By 48" Tall Blank Door	8PG1192-1DE10
15" Wide By 54" Tall Blank Door	8PG1192-1DE11
15" Wide By 60" Tall Blank Door	8PG1192-1DE12
20" Wide By 6" Tall Blank Door	8PG1192-1DE02
20" Wide By 12" Tall Blank Door	8PG1192-1DE13
20" Wide By 18" Tall Blank Door	8PG1192-1DE14
20" Wide By 24" Tall Blank Door	8PG1192-1DE15
20" Wide By 30" Tall Blank Door	8PG1192-1DE16
20" Wide By 36" Tall Blank Door	8PG1192-1DE17

Unit Parts

Door Assembly Kits and Door Parts—Model 95+ and System 89/tiastar

Door, hinges, and mounting hardware included in the Model 95+ and System 89/tiastar Door Assembly Kit.

Door Kit Type (cont.)	Ordering Number
20" Wide By 42" Tall Blank Door	8PG1192-1DE18
20" Wide By 48" Tall Blank Door	8PG1192-1DE20
20" Wide By 54" Tall Blank Door	8PG1192-1DE21
20" Wide By 60" Tall Blank Door	8PG1192-1DE22
20" Wide By 66" Tall Blank Door	8PG1192-1DE23
20" Wide By 72" Tall Blank Door	8PG1192-1DE24
24" Wide By 72" Tall Blank Door	8PG1192-1DE36
30" Wide By 36" Tall Blank Door	8PG1192-1DE25
30" Wide By 42" Tall Blank Door	8PG1192-1DE26
30" Wide By 72" Tall Blank Door	8PG1192-1DE27
30" Wide By 30" Tall Blank Door	8PG1192-1DE28
30" Wide By 24" Tall Blank Door	8PG1192-1DE30
30" Wide By 12" Tall Blank Door	8PG1192-1DE31
30" Wide By 18" Tall Blank Door	8PG1192-1DE32
30" Wide By 48" Tall Blank Door	8PG1192-1DE33
30" Wide By 54" Tall Blank Door	8PG1192-1DE34
30" Wide By 60" Tall Blank Door	8PG1192-1DE35
15" Wide By 12" Tall Door with Handle Opening (for tiastar only)	8PG1192-1DE37
15" Wide By 12" Tall Door with Handle Opening & Reset Assembly (for tiastar only)	8PG1192-1DE38

Door Kit Type (cont.)	Ordering Number
15" Wide By 12" Tall Door with Handle Opening & Pilot Housing Opening (for tiastar only)	8PG1192-1DE40
15" Wide By 12" Tall Door with Handle Opening, Pilot Housing Opening, & Reset Assembly (for tiastar only)	8PG1192-1DE41
15" Wide By 12" Tall Door with Left And Right Handle Openings (for tiastar only)	8PG1192-1DE42
20" Wide Panel Kickplate	8PG1192-1DE43
30" Wide Panel Kickplate	8PG1192-1DE44
High Density (HD) Door Kit Type	Ordering Number
6" HD Unit Door Kit	8PG1192-1DE00
12" High Density (HD) Unit Door with Reset and Pilot Device Housing Opening	8PG1192-1DE45
12" HD Unit Door with Reset	8PG1192-1DE46
12" HD Unit Door with Pilot Device Housing Opening	8PG1192-1DE47
18" HD Unit Door with Reset and Pilot Device Housing Opening	8PG1192-1DE48
18" HD Unit Door with Reset	8PG1192-1DE50
18" HD Unit Door with Pilot Device Housing Opening	8PG1192-1DE51

Unit Parts

Door Assembly Kits and Door Parts—System 89/tiastar

Door Parts	Ordering Number
Barrier Mounting Angle Bracket (Qty 10)	8PG1192-2DF00
tiastar Door Latch And Mounting Kit	8PG1192-2DF01
15" Wide Plug-In Support Assembly Kit	8PG1192-2DF02
20" Wide Plug-In Support Assembly Kit	8PG1192-2DF03
22MM NEMA 1 Pilot Device Housing Kit	8PG1192-1DF04
22MM NEMA 12 Pilot Device Housing Kit	8PG1192-1DF05
30MM NEMA 1 Pilot Device Housing Kit	8PG1192-1DF06
30MM NEMA 12 Pilot Device Housing Kit	8PG1192-1DF07
22MM Flush Hole Plugs For Pilot Device Housing (Qty 4)	8PG1192-1DF08
30MM Flush Hole Plugs For Pilot Device Housing (Qty 4)	8PG1192-1DF10
High Density (HD) Door Parts	Ordering Number
Pilot Device Housing Kit for 12" and 18" High Density Units (Qty 4)	8PG1192-1DF11

tiastar Door Latch and Mounting Kit



Qty (2) hinges and pins, qty (2) 1/4 turn assembly, qty (2) gasket bumper, mounting hardware, and installation guide (not shown).

Pilot Device Housing Kit



Housing and qty (4) flush hole plugs (only 2 are shown in the picture).

Plug-In Support Assembly Kit



Side support bracket, unit support and separator, mounting hardware, gasket bumper, and installation guide (not shown).

Unit Parts

Door Assembly Kits and Door Parts—Model 90/95 and Marq21/2

Door, hinges, and mounting hardware included in the Model 90/95 and Marq21/2 Door Assembly Kit.

Model 90/95 and Marq21/2 Vertical Wireway Door Kit Type	Ordering Number
12"	8PG1092-1DA00
18"	8PG1092-1DA01
24"	8PG1092-1DA02
30"	8PG1092-1DA03
36"	8PG1092-1DA04
48"	8PG1092-1DA05
54"	8PG1092-1DA06
60"	8PG1092-1DA07
72"	8PG1092-1DA08
Model 90/95 Door Parts	
Shelf/Pan Top Assembly	8PG1092-2DC00

Model 90/95 and Marq21/2 Door Kit Type	Ordering Number
15" Wide By 6" Tall Filler Door	8PG1092-1DB00
15" Wide By 12" Tall Blank Door	8PG1092-1DB01
15" Wide By 18" Tall Blank Door	8PG1092-1DB02
15" Wide By 24" Tall Blank Door	8PG1092-1DB03
15" Wide By 30" Tall Blank Door	8PG1092-1DB04
15" Wide By 36" Tall Blank Door	8PG1092-1DB05
15" Wide By 48" Tall Blank Door	8PG1092-1DB07
20" Wide By 6" Tall Filler Door	8PG1092-1DB08
20" Wide By 12" Tall Blank Door	8PG1092-1DB10
20" Wide By 18" Tall Blank Door	8PG1092-1DB11
20" Wide By 24" Tall Blank Door	8PG1092-1DB12
20" Wide By 30" Tall Blank Door	8PG1092-1DB13
20" Wide By 36" Tall Blank Door	8PG1092-1DB14
20" Wide By 48" Tall Blank Door	8PG1092-1DB15
20" Wide By 54" Tall Blank Door	8PG1092-1DB16
20" Wide By 72" Tall Blank Door	8PG1092-1DB17

Unit Parts

Handle Operating Mechanism Kits: Model 95+ and System 89/tiastar

Handle assembly, mounting hardware, and installation guide are included in the Model 95+ and System 89/tiastar Handle Kit.

Model 95+ Handle Kit Type	Ordering Number
125A ITE Circuit Breaker, Plug-in, Left Hand, NEMA 1/NEMA 12	8PG1092-1HD00
125A ITE Circuit Breaker, Plug-in, Right Hand, NEMA 1/NEMA 12	8PG1092-1HD01
250A ITE Circuit Breaker, Plug-in, Left Hand, NEMA 1/NEMA 12	8PG1092-1HD02
250A ITE Circuit Breaker, Plug-in, Right Hand, NEMA 1/NEMA 12	8PG1092-1HD03
400A ITE Circuit Breaker, Plug-in, NEMA 1/ NEMA 12	8PG1092-1HD04
30/60A Fusible Disconnect, Plug-in, Left Hand, NEMA 1/NEMA 12	8PG1092-1HD05
30/60A Fusible Disconnect, Plug-in, Right Hand, NEMA 1/NEMA 12	8PG1092-1HD06
100A Fusible Disconnect, Plug-in, NEMA 1/NEMA 12	8PG1092-1HD07
250A ITE MCS, Plug-in, Right Hand, NEMA 1/NEMA 12	8PG1092-1HD08
125A ITE Circuit Breaker, Fixed Mtd, NEMA 1/NEMA 12	8PG1092-1HD10
250A ITE Circuit Breaker, Fixed Mtd, NEMA 1/NEMA 12	8PG1092-1HD11
400/600A ITE Circuit Breaker, Fixed Mtd, NEMA 1/NEMA 12	8PG1092-1HD12
30/60A Fusible Disconnect, Fixed Mtd, NEMA 1/NEMA 12	8PG1092-1HD13
100A Fusible Disconnect, Fixed Mtd, NEMA 1/NEMA 12	8PG1092-1HD14
250A ITE Molded Case Switch, Fixed Mtd, NEMA 1/NEMA 12	8PG1092-1HD15


System 89/tiastar Handle Kit Type	Ordering Number
800 - 2000A Sentron Circuit Breakers	8PG1192-1HE00
125A Sentron Circuit Breaker, Plug-in	8PG1192-1HE02
250A Sentron Circuit Breaker, Plug-in	8PG1192-1HE03
250A Sentron Circuit Breaker, Fixed Mtd	8PG1192-1HE04
30/60A Fusible Disconnect, Plug-in	8PG1192-1HE05
30/60A Fusible Disconnect, Fixed Mtd.	8PG1192-1HE06
125A Sentron Circuit Breaker, 6" Plug-in, with Reset	8PG1192-1HE10

800-2000A Sentron Breaker Handle Kit



Includes handle assembly, mounting hardware, and installation guide (not shown).

System 89/tiastar Handle Kit



Handle assembly and mounting hardware, and installation guide (not shown).

200A Fusible Disconnect, Plug-in	8PG1192-1HE11
200A Fusible Disconnect, Fixed Mtd	8PG1192-1HE12
100A Fusible Disconnect, Plug-in	8PG1192-1HE13
100A Fusible Disconnect, Fixed Mtd	8PG1192-1HE14
125A EG Circuit Breaker, Plug-in	8PG1192-1HE15
125A EG Circuit Breaker, Fixed Mtd	8PG1192-1HE16
125A EG Circuit Breaker, 6" Innova Plug-in with Reset	8PG1192-1HE17
125A EG Circuit Breaker, 6" Plug-in, without Reset	8PG1192-1HE18
125A EG Circuit Breaker, 6" Sirius Plug-in with Reset	8PG1192-1HE20
125A ED Circuit Breaker, 6" HD Unit	8PG1192-1HE21
400/600A Sentron Circuit Breaker, Plug-in	8PG1192-1HE22
400/600A Sentron Circuit Breaker, Fixed Mtd	8PG1192-1HE23
125A 3VA51 Circuit Breaker, Plug-in	8PG11921HE31
150A/250A 3VA52/61/62 Breaker, Plug-in	8PG11921HE32
400A/600A 3VA53/63/54/64 Breaker Fixed Mount	8PG11921HE33

Unit Parts

Handle Operating Mechanism Kits: Marq21, Model 90, and Model 95

Operator mechanism and installation guide are included with the Marq21, Model 90, and Model 95 Handle Kit.

Marq21 Handle Kit Type	Ordering Number
KB/MCP4	8PG1092-1HA00
30/60/100A Fusible Disconnect	8PG1092-1HA01
200A Fusible Disconnect	8PG1092-1HA02
LB, HLB-MCP5 400A (WH)	8PG1092-1HA03
WH FD6, CLF CB	8PG1092-1HA04
EF/EH/HE	8PG1092-1HA05
WH MC-MA	8PG1092-1HA06
WH NC	8PG1092-1HA07
FJ6/F6/HF6/CLF/H-C-FD (ITE)<92	8PG1092-1HA08
JL HJ LL HL SJL SLL JD HJD LD HLD (ITE)	8PG1092-1HA10
30/60/100A Disconnect (W/ HANDLE AUX IS REQUIRED WH)	8PG1092-1HA11
ED/HED ~10/83-3/84	8PG1092-1HA12
ITE E4-E6	8PG1092-1HA13

Model 90 Handle Kit Type	Ordering Number
ED CB, Left Hand	8PG1092-1HB00
ED CB, Right Hand	8PG1092-1HB01
30/60A Fusible Disconnect, Left Hand	8PG1092-1HB02
30/60A Fusible Disconnect, Right Hand	8PG1092-1HB03
WH 100A Fusible Disconnect, Left Hand	8PG1092-1HB04
WH 100A Fusible Disconnect, Right Hand	8PG1092-1HB05
FD6 CB	8PG1092-1HB06

Model 95 Handle Kit Type	Ordering Number
FD, HFD, CFD CB	8PG1092-1HC00
JD, HJD, CJD, LD, HLD, CLD CB Fixed Mounted	8PG1092-1HC01
FD CB, Sz 5 Draw-out	8PG1092-1HC02
ED CB, Left Hand, Plug-in for Part Winding Assy	8PG1092-1HC04
30/60A Fusible Disconnect, Left Hand, Plug-in for Part Winding Assy	8PG1092-1HC05
ED, HED CB, Plug-in, Left Hand	8PG1092-1HC06
ED, HED CB, Plug-in, Right Hand	8PG1092-1HC07
30/60A Fusible Disconnect, Plug-in, Left Hand	8PG1092-1HC08
30/60A Fusible Disconnect, Plug-in, Right Hand	8PG1092-1HC10
100A Fusible Disconnect, Plug-in, Left Hand	8PG1092-1HC11
100A Fusible Disconnect, Plug-in, Right Hand	8PG1092-1HC12
200A Fusible Disconnect, Plug-in, Left Hand	8PG1092-1HC13
JD CB Drawout Feeder	8PG1092-1HC14

Unit Parts

MCC Control Fuse Kits

10 fuses and an installation guide are included in the MCC Control Fuse Kit.

Class CC 600 V Fuse Kit Type (Qty 10)	Ordering Number
0.3A	8PG1192-2FA00
0.5 A	8PG1192-2FA01
1A	8PG1192-2FA02
1.5 A	8PG1192-2FA03
2A	8PG1192-2FA04
2.5A	8PG1192-2FA05
3A	8PG1192-2FA06
3.5A	8PG1192-2FA07
6A	8PG1192-2FB00
8A	8PG1192-2FB01
10A	8PG1192-2FB02

Replacement Fuses

XFMR VA	600V Type				250V Type
	Primary Voltage				Sec. V
	200/208	240	480	600	120
50	1A	1A	0.5A	0.3A	0.6A
75	2A	1.5A	0.75A	0.5A	1A
100	2.5A	2A	1A	0.75A	1.25A
150	3.5A	3A	1.5A	1A	2A
200	5A	4A	2A	1A	2.5A
250	6A	5A	2.5A	2A	3.2A
300	8A	6A	3A	2.5A	4A

Midget 250 V Fuse Kit Type (Qty 10)	Ordering Number
0.4A	8PG1192-2FC00
0.6A	8PG1192-2FC01
1A	8PG1192-2FC02
1.6A	8PG1192-2FC03
2A	8PG1192-2FC04
3.2A	8PG1192-2FC05
4A	8PG1192-2FC06
4.5A	8PG1192-2FC07
5A	8PG1192-2FC08
6.25A	8PG1192-2FD00
7A	8PG1192-2FD01
10A	8PG1192-2FD02
12A	8PG1192-2FD03
15A	8PG1192-2FD04
20A	8PG1192-2FD05
25A	8PG1192-2FD06

Midget 600 V Fuse Kit Type (Qty 10)	Ordering Number
2.5A	8PG1192-2FE00
4A	8PG1192-2FE01
5A	8PG1192-2FE02
6A	8PG1192-2FE03
8A	8PG1192-2FE04

Unit Parts

MCC Control Parts Kits

Fuse blocks, end barriers, and screws are included in the MCC Control Part Kit.


Fuse Block Kit Type	Ordering Number
Type CC Fuse Block, With Rejection Feature (Qty 3)	8PG1192-2CF00
Type M Fuse Block, Without Rejection Feature (Qty 3)	8PG1192-2CF01

MCC Terminal Blocks Accessory Kit Type	Ordering Number
Terminal Block Accessory Kit	8PG1192-2TA00
Terminal Block Mounting Bracket Kit (for recessed fixed mounted unit)	8PG1192-2TA01

Metering Terminal Block (Qty 1)	Ordering Number
4 Pole, Shorting Terminal Block	8PG1192-2TM00

Control Terminal Blocks (Qty 5)	Ordering Number
4 Pole, Pull Apart, Din Rail Mounted, Control Terminal Block	8PG1192-2TR00
3 Pole, Stationary, Rail Mounted, Control Terminal Block	8PG1192-2TR01
3 Pole, Pull Apart, Rail Mounted	8PG1192-2TR02
3 Pole, Stationary, Rail Mounted, Ring Tongue Only	8PG1192-2TR03
5 Pole, Pull Apart, Screw Mounted (Model 95)	8PG1092-2TB00
3 Pole, Stationary, Screw Mounted	8PG1192-2TB01
5 Pole, Pull Apart, Screw Mounted (Model 95)	8PG1092-2TB00
3 Pole, Stationary, Screw Mounted	8PG1192-2TB01
3 Pole, Pull Apart, Screw Mounted	8PG1192-2TB02
4 Pole, Pull Apart, Swing Plate Mounted, Control Terminal Block	8PG1 192-2TS00

Blank Nameplate Kit



Terminal end retainer, 13-3/4" mounting rail, 14-15/16" din rail, terminal marking strip, and mounting hardware.

MCC High Density Terminal Blocks Kit (Qty 1)	Ordering Number
12 Point Terminal Block Kit For 6" and 12"	8PG1192-2TH00
12 Point Terminal Block Kit For 18"	8PG1192-2TH01
14 Point Terminal Block Kit For 6" and 12"	8PG1192-2TH02
14 Point Terminal Block Kit For 18"	8PG1192-2TH03
16 Point Terminal Block Kit For 12"	8PG1192-2TH04
16 Point Terminal Block Kit For 18"	8PG1192-2TH05
2 Position Insulated Insertion Bridge	8PG1192-2TH06

Power Terminal Blocks (Qty 5)	Ordering Number
3 Pole, Pull Apart, Rail Mounted, 70 Amp	8PG1192-2TP00
3 Pole, Stationary, Rail Mounted, 70 Amp	8PG1192-2TP01
3 Pole, Stationary, Rail Mounted, 125 Amp	8PG1192-2TP02
3 Pole, Pull Apart, Rail Mounted, Ring Tongue Only, 45 Amp	8PG1192-2TP03
3 Pole, Stationary, Rail Mounted, Ring Tongue Only, 115 Amp	8PG1192-2TP04

Swingplate Kit* Type	Ordering Number
12 Inch Unit Side Swingplate Kit	8PG1192-2TS01
18 Inch Unit Side Swingplate (for Din Rail Terminal Block Mounting Kit)	8PG1192-2TS02
18 Inch Unit Side Swingplate Kit	8PG1192-2TS03

* Note: One unit side Swingplate, Grounding spring, and mounting hardware are included in the Swingplate Kit.

Unit Parts

Nameplate, Overload and Shutter Mechanism Kits

Nameplate Kits

Blank Nameplates Kit Type (Qty 5 Nameplates)	Ordering Number
White Blank Nameplate Kit (Black Lettering)	8PG1192-1NA00
Black Blank Nameplate Kit (White Lettering)	8PG1192-1NA01
Red Blank Nameplate Kit (White Lettering)	8PG1192-1NA02
Yellow Blank Nameplate Kit (Black Lettering)	8PG1192-1NA03
Dark Grey Blank Nameplate Kit (White Lettering)	8PG1192-1NA04


Overload Reset Kits

Kit Name	Ordering Number
Standard Reset Assembly Kit (Qty 5)	8PG1192-2RA00
Bi-Metal Only Reset Assembly Kit, Size 4 (Qty 1)	8PG1192-2RA01
Reset Hole Plugs (Qty 10)	8PG1192-2RB00
ESP Reset Extender	49ASRE

Shutter Mechanism Kit


Kit Type	Ordering Number
tiastar Shutter Mechanism Kit	8PG1191-2MA00

Blank Nameplate Kit



1.25" X 3.56" blank nameplate (qty 5), nameplate rivets (qty 10), and screw and nut set (qty 10).

tiastar Shutter Mechanism Kit



Shutter mechanism assembly, mounting hardware, and installation guide (not shown).

Note: The auto-shutter assembly can only be field installed in a Tiastar MCC built with insulated vertical bus manufactured after 6/1/2001.

Miscellaneous Parts

Industrial Control Power Transformers - Class MT

VA	Primary Voltage	Secondary Voltage	Ordering Number
50	208/277	120	MT0050F
50	208/230/460	120	MT0050G
50	220/440	110	MT0050A
	230/460	115	
	240/480	120	
50	550	110	MT0050E
	575	115	
	600	120	
150	220/440	110	MT0150A
	230/460	115	
	240/480	120	
150	550	110	MT0150E
	575	115	
	600	120	
250	220/440	110	MT0250A
	230/460	115	
	240/480	120	
350	220/440	110	MT0350A
	230/460	115	
	240/480	120	
500	220/440	110	MT0500A
	230/460	115	
	240/480	120	

Notes:

1. Includes secondary fuse clip.
2. A primary fuse kit is available for field installation. Ordering Number: KCCFPX2R.
3. For addition control power transformers, please see the Industrial Controls Catalog.


Paint

Paint	Ordering Number
Touch-up Gray Paint 12 oz.	XPT060M

Motor Ground Terminal Kits

Motor Ground Terminal Kits	Ordering Number
For Ring Tongue Terminals	8PG1191-2PM00
Terminal Strip for 4-14 AWG	8PG1191-2PM01

Fuse Clip Kit KCCFPX2R



Note: If you could not find the item that you are looking for in this catalog, please call Customer Service at 1-866-663-7324.

Legal Manufacturer

Siemens Industry, Inc.
7000 Siemens Road
Wendell, North Carolina 27591
United States of America
Telephone: +1 (800) 333-7421
usa.siemens.com/mcc
Order No. SIEA-C40019-01-4AUS

This document contains a general description of available technical options only, and its effectiveness will be subject to specific variables including field conditions and project parameters. Siemens does not make representations, warranties, or assurances as to the accuracy or completeness of the content contained herein. Siemens reserves the right to modify the technology and product specifications in its sole discretion without advance notice.