



Cerberus[®] PRO FC901

Combining innovation and power in a flexible, cost-effective system

The **Cerberus PRO 50 point panel** is an intelligent fire alarm control panel that provides a cost-effective and feature-rich solution for small to mid-size applications.

- Custom system design lets you easily distribute detectors and modules across the building.
- PAD-5 power supply with expanded flexibility in designing multi-floor systems and features like isolation device capability and Siemens patented Boost Technology.
- Mixed functionality loops let you mix and match detectors and modules on circuits.
- Fully compatible with Cerberus PRO advanced, standard, and X series devices, as well as Class X/DCLC (isolation), Class A, Class B, and Class X circuits.

Protect your investment in your existing systems, as the FC901 is backward compatible with Siemens legacy systems and devices. This provides the ability to retain all field devices as you update your control panel.

Access the full Siemens product line, including **ASAt[™] technology** detectors featuring 20+ application specific detection profiles and the industry's only No False Alarm Guarantee. You also benefit from built-in isolation, **ISO[™] technology** on all major addressable devices, providing Class X performance at no added cost.



FC901 Key Benefits

- From simple to relatively complex programming systems, the FC901 has the flexibility to protect your facility
- Supports up to 50 addressable devices on Class A, Class B, or Class X circuits
- Offers the full product line of addressable detectors and devices offered from the Siemens portfolio

SIEMENS

usa.siemens.com/cerberus-pro



Industry-leading Detection

Siemens family of detectors and fire panels provide innovative features and digital intelligence for the most reliable fire alarm system available.

- **Distributed digital intelligence:** Siemens detection devices provide decision making and storage of critical data at the device itself, improving reliability and speed of communication.
- **Full range of detection options:** compatibility with a wide variety of detection options allows the protection of environments, from sensitive to harsh, to be protected with equal reliability.
- The industry's only **No False Alarm Guarantee** offers the earliest possible warning of a fire without the risk of false alarms.



Cerberus PRO

Cerberus PRO is the complete dedicated portfolio for Siemens Fire Partners in the UL/ULC Fire and Life Safety market. Cerberus PRO is a comprehensive portfolio of fire panels, detection and management stations which meet the needs of small-to-large or simple-to-complex applications.

Applications

The FC901 is suitable for a variety small- to mid-size facilities, such as:

- | | | |
|--------------------|------------------------|--------------|
| • Retail Shops | • Strip Malls | • Banks |
| • Doctor's Offices | • Commercial Buildings | • Warehouses |
| • Restaurants | • Convenience Stores | |

Legal Manufacturer

Siemens Industry, Inc.
2 Gatehall Drive
Parsippany, NJ 07054
USA

Telephone: (973) 593-2600

153-SBT-535_en_a
A6V1038540
Printed in the USA
© 05.2024, Siemens Industry, Inc.

SIEMENS